




PRESSALIT®

| | |
|----------------------------|--|
| Product | PLUS 90° angle handrail 400 x 900 mm |
| Item number | RT118035 |
| Colour | <p>VVS:777567635 NRF:6317176 EAN:5708590146300 HMI: 25433 NBS:N13:436 Red (RAL 3003)</p> |
| Product description |  <p>PLUS handrails are high-quality products and they can be combined in countless ways and they provide the final touch to furnishing a functional and flexible bathroom. A reliable solution with many different options, which can easily lay the grounds for increased independence.</p> <p>PLUS handrail, angle 90°, right, diameter 33 mm, A: 400 mm x B: 900 mm, for fixed mounting. The projection of 50 mm from the wall makes it easy to take hold of the rail. Inkl. wall rosette, which covers the fixings. Material: Powder-coated aluminium and plastic Excl. mounting kit.</p> |
| Product capacity | <p>Maximum load: 235 kg. When the handrail is loaded with 235 kg, each wall fastener is loaded with 56 kg. <i>Handrails are tested with a 1.5 safety factor in accordance with the requirements in ISO 17966:2016.</i></p> |
| Materials | <p>Basic material: Aluminium</p> <p>Surface material: Polyester lacquer</p> <p>Cover cap: Cyclopy plastic</p> <p>Strap: Nylon (PA)</p> |
| Ergonomy | <p>The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.</p> |
| Warranty | <p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.</p> |













| | |
|----------------------------------|---|
| Product | PLUS 90° angle handrail 400 x 900 mm |
| Item number | RT118035 |
| Cleaning | <p>Handrails ALU.</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS:</p> <p>Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%</p> <p>NON-DISINFECTANTS:</p> <p>Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p>DECALCIFICATION OF ALUMINUM PARTS:</p> <p>Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts must be wiped over with a damp cloth wrung out in clear water.</p> |
| Declaration of conformity | <p>CE UK MDR This product is in compliance with all relevant requirements of:</p> <p>- Regulation (EU) 2017/745 on medical devices.</p> <p>For the UK: - Medical Device Regulation (MDR) 2002 on medical devices.</p> |



| | |
|--------------------|--------------------------------------|
| Product | PLUS 90° angle handrail 400 x 900 mm |
| Item number | RT118035 |

Installation in different wall types

| | |
|---|--|
|  | <p>Concrete >B25</p> <p>V8617 - Mounting kit, 12 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>  |
|  | <p>Solid Brick >= Mz12</p> <p>V8617 - Mounting kit, 12 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>  |
|  | <p>Solid Sand Lime Brick >= Hlz12</p> <p>V8617 - Mounting kit, 12 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>  |
|  | <p>Aerated Concrete P4</p> <p>V8667 - Mounting kit, 12 bolts M5 x 50 - plugs FTP K 6. To be ordered separately.</p>  |
|  | <p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</p> <p>V8617 - Mounting kit, 12 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.</p>  |



PRESSALIT®

| | |
|--------------------------------------|--|
| Product Item number | PLUS 90° angle handrail 400 x 900 mm RT118035 |
| | <p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</p> <p>Wall fasteners (12 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.</p> |
| | <p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</p> <p>Wall fasteners (12 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.</p> |
| | <p>Drywall (2 x 12,5 mm) water-resistant</p> <p>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.</p> |

pressalit.com