




# PRESSALIT®

<b>Product</b> <b>Item number</b>	PLUS 90° angle handrail 400 x 900 mm RT119108
<b>Colour</b>	VVS:777567508 NRF:6317179 EAN:5708590154039 HMI: 25434 NBS:N13:436 Dark blue (RAL 5011)
<b>Product description</b>	 <p>PLUS handrails are high-quality products and they can be combined in countless ways and they provide the final touch to furnishing a functional and flexible bathroom. A reliable solution with many different options, which can easily lay the grounds for increased independence.</p> <p>PLUS handrail, angle 90°, left, diameter 33 mm, A: 400 mm x B: 900 mm, for fixed mounting.  The projection of 50 mm from the wall makes it easy to take hold of the rail.  Inkl. wall rosette, which covers the fixings.  Material: Powder-coated aluminium and plastic  Excl. mounting kit.</p>
<b>Product capacity</b>	Maximum load: 235 kg. When the handrail is loaded with 235 kg, each wall fastener is loaded with 56 kg. <i>Handrails are tested with a 1.5 safety factor in accordance with the requirements in ISO 17966:2016.</i>
<b>Materials</b>	Basic material: Aluminium  Surface material: Polyester lacquer  Cover cap: Cyclopy plastic  Strap: Nylon (PA)
<b>Ergonomy</b>	The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.













<b>Product</b>	PLUS 90° angle handrail 400 x 900 mm
<b>Item number</b>	RT119108
<b>Cleaning</b>	<p>Handrails ALU.</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p><b>DISINFECTANTS:</b></p> <p>Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%</p> <p><b>NON-DISINFECTANTS:</b></p> <p>Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p><b>DECALCIFICATION OF ALUMINUM PARTS:</b></p> <p>Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts must be wiped over with a damp cloth wrung out in clear water.</p>
<b>Declaration of conformity</b>	<p>CE UK MDR This product is in compliance with all relevant requirements of:</p> <p>- Regulation (EU) 2017/745 on medical devices.</p> <p><b>For the UK:</b> - Medical Device Regulation (MDR) 2002 on medical devices.</p>



PRESSALIT®

<b>Product</b>	PLUS 90° angle handrail 400 x 900 mm
<b>Item number</b>	RT119108

## Installation in different wall types

	<b>Concrete &gt;B25</b> V8617 - Mounting kit, 12 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately. 
	<b>Solid Brick &gt;= Mz12</b> V8617 - Mounting kit, 12 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately. 
	<b>Solid Sand Lime Brick &gt;= Hlz12</b> V8617 - Mounting kit, 12 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately. 
	<b>Aerated Concrete P4</b> V8667 - Mounting kit, 12 bolts M5 x 50 - plugs FTP K 6. To be ordered separately. 
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b> V8617 - Mounting kit, 12 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately. 



# PRESSALIT®

<b>Product</b> <b>Item number</b>	PLUS 90° angle handrail 400 x 900 mm RT119108
	<p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b></p> <p>Wall fasteners (12 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.</p>
	<p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</b></p> <p>Wall fasteners (12 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.</p>
	<p><b>Drywall (2 x 12,5 mm) water-resistant</b></p> <p>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.</p>

pressalit.com