




<b>Product</b> <b>Item number</b>	PLUS handrail section 1200 mm. RT303000
<b>Colour</b>	White
<b>Product description</b>	<p>VVS:777569030 NRF:6311247 EAN:5708590146027 NBS:N13:436</p> <p>RT300 - A = 300 RT303 - A = 1200 RT307 - A = 2400</p>  <p>PLUS hand rail tube. Length 1200 mm, diameter 33 mm. Requires other hand rail elements for installation. <i>Please enquire for special hand rail solutions.</i> Please note that RT360 PLUS hand rail wall mounting with strap must always be installed at all joints of tubes or every 1200 mm.</p> <p>PLUS hand rail tube. Length 1200 mm, diameter 33 mm. Requires other hand rail elements for installation. <i>Please enquire for special hand rail solutions.</i> Please note that RT360 PLUS hand rail wall mounting with strap must always be installed at all joints of tubes or every 1200 mm. Materials: Powder-coated aluminium.</p>
<b>Product capacity</b>	Maximum load: With a span up to 1000 mm: 210 kg With a span up to 1300 mm: 150 kg.
<b>Materials</b>	Basic material: Aluminium Surface material: Polyester lacquer
<b>Ergonomy</b>	The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.
<b>Cleaning</b>	The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.



PRESSALIT®

<b>Product</b>	PLUS handrail section 1200 mm.
<b>Item number</b>	RT303000

---

[www.pressalit.com](http://www.pressalit.com)

---

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

PRESSALIT®