




Product	PLUS handrail section 1200 mm.
Item number	RT303000
Colour	<p>VVS:777569030 NRF:6311247 EAN:5708590146027 NBS:N13:436</p> <p>White</p>
Product description	<p>RT300 - A = 300 RT303 - A = 1200 RT307 - A = 2400</p>  <p>PLUS hand rail tube. Length 1200 mm, diameter 33 mm. Requires other hand rail elements for installation. <i>Please enquire for special hand rail solutions.</i> Please note that RT360 PLUS hand rail wall mounting with strap must always be installed at all joints of tubes or every 1200 mm.</p> <p>PLUS hand rail tube. Length 1200 mm, diameter 33 mm. Requires other hand rail elements for installation. <i>Please enquire for special hand rail solutions.</i> Please note that RT360 PLUS hand rail wall mounting with strap must always be installed at all joints of tubes or every 1200 mm. Materials: Powder-coated aluminium.</p>
Product capacity	<p>Maximum load: With a span up to 1000 mm: 210 kg With a span up to 1300 mm: 150 kg.</p>
Materials	<p>Basic material: Aluminium</p> <p>Surface material: Polyester lacquer</p>
Ergonomy	<p>The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.</p>
Warranty	<p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.</p>
Cleaning	<p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.</p>



PRESSALIT®

Product	PLUS handrail section 1200 mm.
Item number	RT303000

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®