



# PRESSALIT®

<b>Product</b> <b>Item number</b>	PLUS grab bar section 17.9" RT303000
<b>Color</b>	VVS:777569030 NRF:6311247 EAN:5708590146027 NBS:N13:436  White
<b>Product description</b>	<p>PLUS grab bar tube, incl. connecting unit with male and female joints Length 17.9", diameter 1.3". Requires other grab bar elements for installation. <i>Please enquire for special grab bar solutions.</i> Please note that RT360 PLUS grab bar wall mounting with strap must always be installed at all joints of tubes or every 47".</p> <p>PLUS grab bar tube, incl. connecting unit with male and female joints Length 17.9", diameter 1.3". Requires other grab bar elements for installation. <i>Please enquire for special grab bar solutions.</i> Please note that RT360 PLUS grab bar wall mounting with strap must always be installed at all joints of tubes or every 47". Materials: Powder-coated aluminium.</p>
<b>Product capacity</b>	Maximum load: With a span up to 39.4" : 460 lbs. With a span up to 51.2" : 330 lbs.
<b>Materials</b>	Core material: Aluminium Surface material: Polyester lacquer
<b>Ergonomy</b>	The 1.3" diameter enables the rail to be held comfortably and firmly. The projection of 2" from the wall makes it easy to take hold of the rail.
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.
<b>Cleaning</b>	This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.



# PRESSALIT®

<b>Product</b>	PLUS grab bar section 17.9"
<b>Item number</b>	RT303000

---

[pressalit.com](http://pressalit.com)

---

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®