




Product Item number	PLUS handrail section 1200 mm. RT303035
Colour	VVS:777569035 EAN:5708590146034 NBS:N13:436 Red (RAL 3003)
Product description	<div> <div> RT300 - A = 300 RT303 - A = 1200 RT307 - A = 2400 </div>  </div> <p>PLUS hand rail tube. Length 1200 mm, diameter 33 mm. Requires other hand rail elements for installation. <i>Please enquire for special hand rail solutions.</i> Please note that RT360 PLUS hand rail wall mounting with strap must always be installed at all joints of tubes or every 1200 mm.</p> <p>PLUS hand rail tube. Length 1200 mm, diameter 33 mm. Requires other hand rail elements for installation. <i>Please enquire for special hand rail solutions.</i> Please note that RT360 PLUS hand rail wall mounting with strap must always be installed at all joints of tubes or every 1200 mm. Materials: Powder-coated aluminium.</p>
Product capacity	Maximum load: With a span up to 1000 mm: 210 kg With a span up to 1300 mm: 150 kg.
Materials	Basic material: Aluminium Surface material: Polyester lacquer
Ergonomy	The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.
Cleaning	The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.



PRESSALIT®

Product	PLUS handrail section 1200 mm.
Item number	RT303035

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®