




|                            |   |
|----------------------------|---|
| <b>Product</b>             | PLUS handrail section 2400 mm.  |
| <b>Item number</b>         | RT307000  |
| <b>Colour</b>              | White   |
| <b>Product description</b> | <p>VVS:777569070<br/>NRF:6311249<br/>EAN:5708590146102<br/>NBS:N13:436</p> <p>RT300 - A = 300<br/>RT303 - A = 1200<br/>RT307 - A = 2400</p>  <p>PLUS hand rail tube.<br/>Length 2400 mm, diameter 33 mm.<br/>Requires other hand rail elements for installation.<br/><i>Please enquire for special hand rail solutions.</i><br/>Please note that RT360 PLUS hand rail wall mounting with strap must always be installed at all joints of tubes or every 1200 mm.</p> <p>PLUS hand rail tube.<br/>Length 2400 mm, diameter 33 mm.<br/>Requires other hand rail elements for installation.<br/><i>Please enquire for special hand rail solutions.</i><br/>Please note that RT360 PLUS hand rail wall mounting with strap must always be installed at all joints of tubes or every 1200 mm.<br/>Materials: Powder-coated aluminium.</p> |
| <b>Product capacity</b>    | Maximum load: With a span up to 1000 mm: 210 kg<br>With a span up to 1300 mm: 150 kg.   |
| <b>Materials</b>           | Basic material: Aluminium<br>Surface material: Polyester lacquer  |
| <b>Ergonomy</b>            | The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.  |
| <b>Warranty</b>            | Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.   |
| <b>Cleaning</b>            | The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.  |



# PRESSALIT®

|                    |                                |
|--------------------|--------------------------------|
| <b>Product</b>     | PLUS handrail section 2400 mm. |
| <b>Item number</b> | RT307000                       |

---

[pressalit.com](http://pressalit.com)

---

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

PRESSALIT®