




<p>Product Item number</p>	<p>PLUS handrail section 2400 mm. RT307108</p>
<p>Colour Product description</p>	<p>VVS:777569078 EAN:5708590153698 NBS:N13:436</p> <p>Dark blue (RAL 5011)</p>  <p>RT300 - A = 300 RT303 - A = 1200 RT307 - A = 2400</p> <p>PLUS hand rail tube. Length 2400 mm, diameter 33 mm. Requires other hand rail elements for installation. <i>Please enquire for special hand rail solutions.</i> Please note that RT360 PLUS hand rail wall mounting with strap must always be installed at all joints of tubes or every 1200 mm.</p> <p>PLUS hand rail tube. Length 2400 mm, diameter 33 mm. Requires other hand rail elements for installation. <i>Please enquire for special hand rail solutions.</i> Please note that RT360 PLUS hand rail wall mounting with strap must always be installed at all joints of tubes or every 1200 mm. Materials: Powder-coated aluminium.</p>
<p>Product capacity</p>	<p>Maximum load: With a span up to 1000 mm: 210 kg With a span up to 1300 mm: 150 kg.</p>
<p>Materials Ergonomy</p>	<p>Basic material: Aluminium</p> <p>Surface material: Polyester lacquer</p> <p>The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.</p>
<p>Warranty Cleaning</p>	<p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.</p>



PRESSALIT®

Product	PLUS handrail section 2400 mm.
Item number	RT307108

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®