



| | |
|--------------------------------------|---|
| Product Item number | PLUS grab bar section 94.5" RT307108 |
| Color | VVS:777569078 EAN:5708590153698 NBS:N13:436 Dark blue (RAL 5011) |
| Product description | <p>PLUS grab bar tube, incl. connecting unit with male and female joints Length 94.5", diameter 1.3". Requires other grab bar elements for installation. <i>Please enquire for special grab bar solutions.</i> Please note that RT360 PLUS grab bar wall mounting with strap must always be installed at all joints of tubes or every 47".</p> <p>PLUS grab bar tube, incl. connecting unit with male and female joints Length 94.5", diameter 1.3". Requires other grab bar elements for installation. <i>Please enquire for special grab bar solutions.</i> Please note that RT360 PLUS grab bar wall mounting with strap must always be installed at all joints of tubes or every 47". Materials: Powder-coated aluminium.</p> |
| Product capacity | Maximum load: With a span up to 39.4" : 460 lbs. With a span up to 51.2" : 330 lbs. |
| Materials Ergonomy | Core material: Aluminium Surface material: Polyester lacquer The 1.3" diameter enables the rail to be held comfortably and firmly. The projection of 2" from the wall makes it easy to take hold of the rail. |
| Warranty Cleaning | Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date. This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged. |



PRESSALIT®

| | |
|--------------------|-----------------------------|
| Product | PLUS grab bar section 94.5" |
| Item number | RT307108 |

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®