



<b>Product</b> <b>Item number</b>	PLUS grab bar section 23.9", incl. wall rosette RT321000
<b>Color</b>	VVS:777569210 NRF:6311254 EAN:5708590146539 NBS:N13:436  White
<b>Product description</b>	<p>PLUS grab bar tube, with wall rosette and connecting unit female joint. Length 23.9", diameter 1.3". Requires other grab bar elements for installation. <i>Please enquire for special grab bar solutions.</i> Please note that RT360 PLUS grab bar wall mounting with strap must always be installed at all joints of tubes or every 47". Excl. mounting kit. See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p> <p>PLUS grab bar tube, with wall rosette and connecting unit female joint. Length 23.9", diameter 1.3". Requires other grab bar elements for installation. <i>Please enquire for special grab bar solutions.</i> Please note that RT360 PLUS grab bar wall mounting with strap must always be installed at all joints of tubes or every 47". Materials: Powder-coated aluminium and plastics. Excl. mounting kit.</p>
<b>Product capacity</b>	Maximum load: With a span up to 39.4" : 460 lbs. With a span up to 51.2" : 330 lbs.
<b>Materials</b>	Core material: Aluminium Surface material: Polyester lacquer Cover cap: Cyclopy plastic
<b>Ergonomy</b>	The 1.3" diameter enables the rail to be held comfortably and firmly. The projection of 2" from the wall makes it easy to take hold of the rail.
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.
<b>Cleaning</b>	This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.











<b>Product</b>	PLUS grab bar section 23.9", incl. wall rosette
<b>Item number</b>	RT321000

## Mounting in different wall types

	<b>Concrete &gt;B25</b> V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	<b>Solid Brick &gt;= Mz12</b> V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	<b>Solid Sand Lime Brick &gt;= Hlz12</b> V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	<b>Aerated Concrete P4</b> V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6, for aerated concrete. To be ordered separately.	
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b> V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.	



# PRESSALIT®

Product Item number	PLUS grab bar section 23.9", incl. wall rosette RT321000		
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b> Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.		
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch)</b> Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.		
	<b>Drywall (2 x 12,5 mm) water-resistant</b> Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.		

pressalit.com

Pressalit A/S  
 Pressalitvej 1  
 DK-8680 Ry  
 Tel.: +45 8788 8788  
 Fax: +45 8788 8789  
 E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®