



PRESSALIT®

Product Item number	PLUS grab bar section 41.2", incl. wall rosette RT323000
Color	VVS:777569230 NRF:6311258 EAN:5708590146577 NBS:N13:436 White
Product description	<p>PLUS grab bar tube, with wall rosette and connecting unit female joint. Length 41.2", diameter 1.3". Requires other grab bar elements for installation. <i>Please enquire for special grab bar solutions.</i> Please note that RT360 PLUS grab bar wall mounting with strap must always be installed at all joints of tubes or every 47". Excl. mounting kit. See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p> <p>PLUS grab bar tube, with wall rosette and connecting unit female joint. Length 41.2", diameter 1.3". Requires other grab bar elements for installation. <i>Please enquire for special grab bar solutions.</i> Please note that RT360 PLUS grab bar wall mounting with strap must always be installed at all joints of tubes or every 47". Materials: Powder-coated aluminium and plastics. Excl. mounting kit.</p>
Product capacity	Maximum load: With a span up to 39.4" : 460 lbs. With a span up to 51.2" : 330 lbs.
Materials	Core material: Aluminium Surface material: Polyester lacquer Cover cap: Cyclopy plastic
Ergonomy	The 1.3" diameter enables the rail to be held comfortably and firmly. The projection of 2" from the wall makes it easy to take hold of the rail.
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.
Cleaning	This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.











Product	PLUS grab bar section 41.2", incl. wall rosette
Item number	RT323000

Mounting in different wall types

	<p>Concrete >B25</p> <p>V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>	
	<p>Solid Brick >= Mz12</p> <p>V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>	
	<p>Solid Sand Lime Brick >= Hlz12</p> <p>V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>	
	<p>Aerated Concrete P4</p> <p>V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6, for aerated concrete. To be ordered separately.</p>	
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</p> <p>V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.</p>	



PRESSALIT®

Product Item number	PLUS grab bar section 41.2", incl. wall rosette RT323000		
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.		
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch) Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.		
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.		

pressalit.com

Pressalit A/S
 Pressalitvej 1
 DK-8680 Ry
 Tel.: +45 8788 8788
 Fax: +45 8788 8789
 E-mail: pressalit@pressalit.com

PRESSALIT®