




<b>Product</b> <b>Item number</b>	PLUS handrail section 1046 mm, incl. wall rosette RT323035
<b>Colour</b>	VVS:777569235 EAN:5708590146584 NBS:N13:436  Red (RAL 3003)
<b>Product description</b>	<div> <div>           RT320 - A = 321            RT321 - A = 608            RT322 - A = 746            RT323 - A = 1046         </div>  </div> <p>PLUS hand rail tube, with wall rosette and connecting unit female joint.          Length 1046 mm, diameter 33 mm.          Requires other hand rail elements for installation.  <i>Please enquire for special hand rail solutions.</i>          Please note that RT360 PLUS hand rail wall mounting with strap must always be installed at all joints of tubes or every 1200 mm.          Excl. mounting kit.          See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p> <p>PLUS hand rail tube, with wall rosette and connecting unit female joint.          Length 1046 mm, diameter 33 mm.          Requires other hand rail elements for installation.  <i>Please enquire for special hand rail solutions.</i>          Please note that RT360 PLUS hand rail wall mounting with strap must always be installed at all joints of tubes or every 1200 mm.          Materials: Powder-coated aluminium and plastics.          Excl. mounting kit.</p>
<b>Product capacity</b>	Maximum load: With a span up to 1000 mm: 210 kg With a span up to 1300 mm: 150 kg.
<b>Materials</b>	Basic material: Aluminium  Surface material: Polyester lacquer  Cover cap: Cyclopy plastic
<b>Ergonomy</b>	The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.



# PRESSALIT®

<b>Product</b>	PLUS handrail section 1046 mm, incl. wall rosette
<b>Item number</b>	RT323035
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.
<b>Cleaning</b>	The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.











<b>Product</b>	PLUS handrail section 1046 mm, incl. wall rosette
<b>Item number</b>	RT323035

## Installation in different wall types

	<b>Concrete &gt;B25</b> V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	<b>Solid Brick &gt;= Mz12</b> V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	<b>Solid Sand Lime Brick &gt;= Hlz12</b> V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	<b>Aerated Concrete P4</b> V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6. To be ordered separately.	
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b> V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.	



# PRESSALIT®

Product Item number	PLUS handrail section 1046 mm, incl. wall rosette RT323035		
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b> Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.		
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</b> Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.		
	<b>Drywall (2 x 12,5 mm) water-resistant</b> Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.		

pressalit.com

Pressalit A/S  
 Pressalitvej 1  
 DK-8680 Ry  
 Tel.: +45 8788 8788  
 Fax: +45 8788 8789  
 E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®