




<p><b>Product</b> <b>Item number</b></p>	<p>PLUS handrail section 652 mm, incl. wall rosette and strap RT331000</p>
<p><b>Colour</b>  <b>Product description</b></p>	<p>VVS:777569310 NRF:6311263 EAN:5708590146614 NBS:N13:436</p> <p>White</p>  <p>RT330 - A = 365 RT331 - A = 662 RT332 - A = 790 RT333 - A = 1090</p> <p>PLUS hand rail tube, with wall rosette and strop. Length 652 mm, diameter 33 mm. Requires other hand rail elements for installation. <i>Please enquire for special hand rail solutions.</i> Excl. mounting kit. See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p> <p>PLUS hand rail tube, with wall rosette and strop. Length 652 mm, diameter 33 mm. Requires other hand rail elements for installation. <i>Please enquire for special hand rail solutions.</i> Materials: Powder-coated aluminium and plastics. Excl. mounting kit.</p>
<p><b>Product capacity</b></p>	<p>Maximum load: With a span up to 1000 mm: 210 kg With a span up to 1300 mm: 150 kg.</p>
<p><b>Materials</b>  <b>Ergonomy</b></p>	<p>Basic material: Aluminium</p> <p>Surface material: Polyester lacquer</p> <p>Cover cap: Cyclopy plastic</p> <p>Strap: Nylon (PA)</p> <p>The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.</p>
<p><b>Warranty</b></p>	<p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.</p>



# PRESSALIT®

<b>Product</b>	PLUS handrail section 652 mm, incl. wall rosette and strap
<b>Item number</b>	RT331000
<b>Cleaning</b>	The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.








<b>Product</b>	PLUS handrail section 652 mm, incl. wall rosette and strap
<b>Item number</b>	RT331000

## Installation in different wall types

	<p><b>Concrete &gt;B25</b> V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>	
	<p><b>Solid Brick &gt;= Mz12</b> V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>	
	<p><b>Solid Sand Lime Brick &gt;= Hlz12</b> V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>	
	<p><b>Aerated Concrete P4</b> V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6. To be ordered separately.</p>	
	<p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b> V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.</p>	



<b>Product</b> <b>Item number</b>	PLUS handrail section 652 mm, incl. wall rosette and strap RT331000	
	<p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b></p> <p>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.</p>	
	<p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</b></p> <p>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.</p>	
	<p><b>Drywall (2 x 12,5 mm) water-resistant</b></p> <p>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.</p>	