



<b>Product</b> <b>Item number</b>	PLUS grab bar section 31.1", incl. wall rosette and strap RT332108
<b>Color</b>	VVS:777569328 EAN:5708590153810 NBS:N13:436  Dark blue (RAL 5011)
<b>Product description</b>	<p>PLUS grab bar tube, with wall rosette and strap. Length 31.1", diameter 1.3". Requires other grab bar elements for installation. <i>Please enquire for special grab bar solutions.</i> Excl. mounting kit. See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p> <p>PLUS grab bar tube, with wall rosette and strap. Length 31.1", diameter 1.3". Requires other grab bar elements for installation. <i>Please enquire for special grab bar solutions.</i> Materials: Powder-coated aluminium and plastics. Excl. mounting kit.</p>
<b>Product capacity</b>	Maximum load: With a span up to 39.4" : 460 lbs. With a span up to 51.2" : 330 lbs.
<b>Materials</b>	Core material: Aluminium Surface material: Polyester lacquer Cover cap: Cyclopy plastic Strap: Nylon (PA)
<b>Ergonomy</b>	The 1.3" diameter enables the rail to be held comfortably and firmly. The projection of 2" from the wall makes it easy to take hold of the rail.
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.
<b>Cleaning</b>	This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.



PRESSALIT®









<b>Product</b>	PLUS grab bar section 31.1", incl. wall rosette and strap
<b>Item number</b>	RT332108

## Mounting in different wall types

	<b>Concrete &gt;B25</b> V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	<b>Solid Brick &gt;= Mz12</b> V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	<b>Solid Sand Lime Brick &gt;= Hlz12</b> V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	<b>Aerated Concrete P4</b> V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6, for aerated concrete. To be ordered separately.	
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b> V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.	



# PRESSALIT®

Product Item number	PLUS grab bar section 31.1", incl. wall rosette and strap RT332108		
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b> Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.		
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch)</b> Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.		
	<b>Drywall (2 x 12,5 mm) water-resistant</b> Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.		

pressalit.com

Pressalit A/S  
 Pressalitvej 1  
 DK-8680 Ry  
 Tel.: +45 8788 8788  
 Fax: +45 8788 8789  
 E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®