








Product	PLUS handrail section 1090 mm, incl. wall rosette and strap. (C)	
Item number	<p>RT333000 VVS:777569330 NRF:6311267 EAN:5708590146645 NBS:N13:436</p>	<p>RT330 - A = 365 RT331 - A = 662 RT332 - A = 790 RT333 - A = 1090</p>
Colour	White	
Product description	<p>PLUS hand rail tube, with wall rosette and stop. Length 1090 mm, diameter 33 mm. Requires other hand rail elements for installation. <i>Please enquire for special hand rail solutions.</i> Excl. fixing kit. See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p>	
Adjustment height		
Product capacity	<p>Maximum load: With a span up to 1000 mm: 210 kg With a span up to 1300 mm: 150 kg.</p>	
Materials	<p>Basic material: Aluminium Surface material: Polyester lacquer Cover cap: Cycoloy plastic Strap: Nylon (PA)</p>	
Ergonomy	<p>The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.</p>	
Warranty	<p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.</p>	
Cleaning	<p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.</p>	










Product	PLUS handrail section 1090 mm, incl. wall rosette and strap. (C)
----------------	------------------------------------------------------------------

Installation in different wall types

	Concrete >B25 V8615 - Fixing kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.
	Solid Brick >= Mz12 V8615 - Fixing kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.
	Solid Sand Lime Brick >= Hlz12 V8615 - Fixing kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.
	Aerated Concrete P4 V8665 - Fixing kit, 4 bolts M5 x 50 - plugs FTP K 6. To be ordered separately.
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8615 - Fixing kit, 4 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.





Product	PLUS handrail section 1090 mm, incl. wall rosette and strap. (C)	
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</p> <p>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.</p>	<p>fischer KD 8 snaptight wingit</p> 
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</p> <p>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.</p>	<p>fischer KD 8 snaptight wingit</p> 
	<p>Drywall (2 x 12,5 mm) water-resistant</p> <p>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.</p>	