



| | |
|--------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Item number | PLUS grab bar section 42.9", incl. wall rosette and strap RT333108 |
| Color | VVS:777569338 EAN:5708590153827 NBS:N13:436 Dark blue (RAL 5011) |
| Product description | <p>PLUS grab bar tube, with wall rosette and strap. Length 42.9", diameter 1.3". Requires other grab bar elements for installation. <i>Please enquire for special grab bar solutions.</i> Excl. mounting kit. See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p> <p>PLUS grab bar tube, with wall rosette and strap. Length 42.9", diameter 1.3". Requires other grab bar elements for installation. <i>Please enquire for special grab bar solutions.</i> Materials: Powder-coated aluminium and plastics. Excl. mounting kit.</p> |
| Product capacity | Maximum load: With a span up to 39.4" : 460 lbs. With a span up to 51.2" : 330 lbs. |
| Materials | Core material: Aluminium Surface material: Polyester lacquer Cover cap: Cyclopy plastic Strap: Nylon (PA) |
| Ergonomy | The 1.3" diameter enables the rail to be held comfortably and firmly. The projection of 2" from the wall makes it easy to take hold of the rail. |
| Warranty | Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date. |
| Cleaning | This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged. |











| | |
|--------------------|-----------------------------------------------------------|
| Product | PLUS grab bar section 42.9", incl. wall rosette and strap |
| Item number | RT333108 |

Mounting in different wall types

| | | |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|  | Concrete >B25 V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately. |  |
|  | Solid Brick >= Mz12 V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately. |  |
|  | Solid Sand Lime Brick >= Hlz12 V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately. |  |
|  | Aerated Concrete P4 V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6, for aerated concrete. To be ordered separately. |  |
|  | Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately. |  |



PRESSALIT®

| Product Item number | PLUS grab bar section 42.9", incl. wall rosette and strap RT333108 | | |
|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|  | Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar. |  |  |
|  | Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch) Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar. |  |  |
|  | Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls. |  | |

pressalit.com

Pressalit A/S
 Pressalitvej 1
 DK-8680 Ry
 Tel.: +45 8788 8788
 Fax: +45 8788 8789
 E-mail: pressalit@pressalit.com

PRESSALIT®