



# PRESSALIT®

<b>Product</b> <b>Item number</b>	PLUS angle grab bar section 15.8" x 6", incl. wall rosette RT340035
<b>Color</b>	VVS:777569405 EAN:5708590146669 NBS:N13:436  Red (RAL 3003)
<b>Product description</b>	<p>PLUS angle grab bar tube, right, 90° angle with one wall rosette and connecting unit male joint. 15.8" x 6", diameter 1.3". Requires other grab bar elements for installation. <i>Please enquire for special grab bar solutions.</i> Please note that RT360 PLUS grab bar wall mounting with strap must always be installed at all joints of tubes or every 47". Excl. mounting kit. See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p> <p>PLUS angle grab bar tube, right, 90° angle with one wall rosette and connecting unit male joint. 15.8" x 6", diameter 1.3". Requires other grab bar elements for installation. <i>Please enquire for special grab bar solutions.</i> Please note that RT360 PLUS grab bar wall mounting with strap must always be installed at all joints of tubes or every 47". Materials: Powder-coated aluminium and plastics. Excl. mounting kit.</p>
<b>Product capacity</b>	Maximum load: With a span up to 39.4" : 460 lbs. With a span up to 51.2" : 330 lbs.
<b>Materials</b>	Core material: Aluminium Surface material: Polyester lacquer Cover cap: Cyclopy plastic
<b>Ergonomy</b>	The 1.3" diameter enables the rail to be held comfortably and firmly. The projection of 2" from the wall makes it easy to take hold of the rail.
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.



# PRESSALIT®











<b>Product</b>	PLUS angle grab bar section 15.8" x 6", incl. wall rosette
<b>Item number</b>	RT340035
<b>Cleaning</b>	This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.



PRESSALIT®









<b>Product</b>	PLUS angle grab bar section 15.8" x 6", incl. wall rosette
<b>Item number</b>	RT340035

## Mounting in different wall types

	<b>Concrete &gt;B25</b> V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	<b>Solid Brick &gt;= Mz12</b> V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	<b>Solid Sand Lime Brick &gt;= Hlz12</b> V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	<b>Aerated Concrete P4</b> V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6, for aerated concrete. To be ordered separately.	
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b> V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.	



# PRESSALIT®

Product Item number	PLUS angle grab bar section 15.8" x 6", incl. wall rosette RT340035		
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b> Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.		
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch)</b> Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.		
	<b>Drywall (2 x 12,5 mm) water-resistant</b> Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.		

pressalit.com

Pressalit A/S  
 Pressalitvej 1  
 DK-8680 Ry  
 Tel.: +45 8788 8788  
 Fax: +45 8788 8789  
 E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®