














<b>Product</b>	PLUS fitting with strap
<b>Item number</b>	RT360035
<b>Colour</b>	<p>VVS: 777569605 EAN: 5708590146737 NBS: N13:436</p> <p>Red (RAL 3003)</p> 
<b>Product description</b>	<p>PLUS hand rail wall mounting with strap. For assembling tubes with diameter 33 mm. Requires other hand rail elements for installation. <i>Please enquire for special hand rail solutions.</i> Excl. mounting kit. See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p> <p>PLUS hand rail wall mounting with strap. For assembling tubes with diameter 33 mm. Requires other hand rail elements for installation. <i>Please enquire for special hand rail solutions.</i> Materials: Plastics. Excl. mounting kit.</p>
<b>Product capacity</b>	<p>Maximum load: With a span up to 1000 mm: 210 kg With a span up to 1300 mm: 150 kg.</p>
<b>Materials</b>	<p>Cover cap: Cyclopy plastic</p> <p>Strap: Nylon (PA)</p>
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.
<b>Cleaning</b>	The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.



PRESSALIT®











<b>Product</b>	PLUS fitting with strap
<b>Item number</b>	RT360035

## Installation in different wall types

	<p><b>Concrete &gt;B25</b></p> <p>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>	
	<p><b>Solid Brick &gt;= Mz12</b></p> <p>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>	
	<p><b>Solid Sand Lime Brick &gt;= Hlz12</b></p> <p>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>	
	<p><b>Aerated Concrete P4</b></p> <p>V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6. To be ordered separately.</p>	
	<p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b></p> <p>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.</p>	



# PRESSALIT®

Product Item number	PLUS fitting with strap RT360035		
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b> Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.		 
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</b> Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.		 
	<b>Drywall (2 x 12,5 mm) water-resistant</b> Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.		

[pressalit.com](http://pressalit.com)