



PRESSALIT®

Product Item number	PLUS fitting with strap RT360108
Color	VVS:777569608 EAN:5708590153872 NBS:N13:436 Dark blue (RAL 5011)
Product description	<p>PLUS grab bar wall mounting with strap. For assembling tubes with diameter 1.3". Requires other grab bar elements for installation. <i>Please enquire for special grab bar solutions.</i> Excl. mounting kit. See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p> <p>PLUS grab bar wall mounting with strap. For assembling tubes with diameter 1.3". Requires other grab bar elements for installation. <i>Please enquire for special grab bar solutions.</i> Materials: Plastics. Excl. mounting kit.</p>
Product capacity	Maximum load: With a span up to 39.4" : 460 lbs. With a span up to 51.2" : 330 lbs.
Materials	Cover cap: Cyclopy plastic Strap: Nylon (PA)
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.
Cleaning	This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.



PRESSALIT®









Product	PLUS fitting with strap
Item number	RT360108

Mounting in different wall types

	<p>Concrete >B25</p> <p>V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>	
	<p>Solid Brick >= Mz12</p> <p>V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>	
	<p>Solid Sand Lime Brick >= Hlz12</p> <p>V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>	
	<p>Aerated Concrete P4</p> <p>V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6, for aerated concrete. To be ordered separately.</p>	
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</p> <p>V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.</p>	



PRESSALIT®

Product Item number	PLUS fitting with strap RT360108		
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.		
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch) Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.		
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.		

pressalit.com

Pressalit A/S
 Pressalitvej 1
 DK-8680 Ry
 Tel.: +45 8788 8788
 Fax: +45 8788 8789
 E-mail: pressalit@pressalit.com

PRESSALIT®