














PRESSALIT®

| | |
|----------------------------|--|
| Product | PLUS fitting with strap and joint |
| Item number | RT361108 |
| Colour | <p>VVS:777569618 EAN:5708590153889 NBS:N13:436</p> <p>Dark blue (RAL 5011)</p>  |
| Product description | <p>PLUS hand rail wall mounting with strap and tube connector, male and female joint. For assembling tubes with diameter 33 mm. Requires other hand rail elements for installation. <i>Please enquire for special hand rail solutions.</i></p> <p>Excl. mounting kit. See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p> <p>PLUS hand rail wall mounting with strap and tube connector, male and female joint. For assembling tubes with diameter 33 mm. Requires other hand rail elements for installation. <i>Please enquire for special hand rail solutions.</i></p> <p>Materials: Plastics. Excl. mounting kit.</p> |
| Product capacity | <p>Maximum load: With a span up to 1000 mm: 210 kg With a span up to 1300 mm: 150 kg.</p> |
| Materials | <p>Cover cap: Cicoloy plastic</p> <p>Strap: Nylon (PA)</p> <p>Connecting unit: Polyphenylene oxide (PPO)</p> |
| Warranty | Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date. |
| Cleaning | The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged. |













| | |
|--------------------|-----------------------------------|
| Product | PLUS fitting with strap and joint |
| Item number | RT361108 |

Installation in different wall types

| | | |
|---|---|---|
|  | <p>Concrete >B25</p> <p>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p> |  |
|  | <p>Solid Brick >= Mz12</p> <p>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p> |  |
|  | <p>Solid Sand Lime Brick >= Hlz12</p> <p>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p> |  |
|  | <p>Aerated Concrete P4</p> <p>V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6. To be ordered separately.</p> |  |
|  | <p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</p> <p>V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.</p> |  |



| Product Item number | PLUS fitting with strap and joint RT361108 | | |
|---|--|---|---|
|  | Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar. |  |   |
|  | Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm) Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar. |  |   |
|  | Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls. |  | |