














Product Item number	PLUS wall track, 600 mm R9806112	
Colour Product description	VVS:615841106 NRF:7501013 EAN:5708590305738 HMI: 71739 Anthracite grey PLUS wall tracks are used for mounting of support arms, shower seats and wash basin brackets, and allows sideways adjustment of these products. See below a selection of products for fitting to the wall track. PLUS wall track, 600 mm, for horizontal mounting. The cover plate hides bolts and wires and facilitates cleaning. Materials: Aluminium and polystyrene. Excl. mounting kit.	
Adjustability Product capacity	Fixed mounting Maximum load: Up to 1000 kg depending on the wall type.	
Materials Ergonomy Features	The wall track is primarily made of 10-micrometre anodized aluminium. The cover plate is made of polystyrene and the ends of the track are capped with ABS polymer. The track distributes the weight of the individual bathroom product, for example a wash basin bracket, along its entire length. The products can be adjusted and locked on to the track with intuitive locking functions. The horizontal track makes it possible to shift the product along the wall to constantly optimize the available space in the bathroom. The front cover plate conceals mounting bolts and any cables.	
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.	



Product	PLUS wall track, 600 mm
Item number	R9806112

Installation in different wall types

	<p>Concrete >B25</p> <p>V8620 - Mounting kit, 3 coach screws Ø8 x 70, plugs SX10. To be ordered separately.</p>	
	<p>Solid Brick >= Mz12</p> <p>V8620 - Mounting kit, 3 coach screws Ø8 x 70, plugs SX10. To be ordered separately.</p>	
	<p>Solid Sand Lime Brick >= Hlz12</p> <p>V8620 - Mounting kit, 3 coach screws Ø8 x 70, plugs SX10. To be ordered separately.</p>	
	<p>Aerated Concrete P4</p> <p>V8670 - Mounting kit, 3 bolts M8 x 35, plugs FTP M 8. To be ordered separately.</p>	
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</p> <p>V8620 - Mounting kit, 3 coach screws Ø8 x 70, plugs SX10. NB! Plugs are not needed. To be ordered separately.</p>	



PRESSALIT®

Product	PLUS wall track, 600 mm
Item number	R9806112

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®