




Product Item number	PLUS anglehandrail section 400 x 154 mm, incl. wall rosette RT341112
Colour	Anthracite grey
Product description	<p> VVS:777569412 NRF:6311273 EAN:5708590318943 NBS:N13:436 </p>  <p> PLUS angle hand rail tube, left, 90° angle with one wall rosette and connecting unit male joint. 400 x 154 mm, diameter 33 mm. Requires other hand rail elements for installation. <i>Please enquire for special hand rail solutions.</i> Please note that RT360 PLUS hand rail wall mounting with strap must always be installed at all joints of tubes or every 1200 mm. Excl. mounting kit. See Technical datasheet (pdf) for information on fixings suitable for various wall types. </p> <p> PLUS angle hand rail tube, left, 90° angle with one wall rosette and connecting unit male joint. 400 x 154 mm, diameter 33 mm. Requires other hand rail elements for installation. <i>Please enquire for special hand rail solutions.</i> Please note that RT360 PLUS hand rail wall mounting with strap must always be installed at all joints of tubes or every 1200 mm. Materials: Powder-coated aluminium and plastics. Excl. mounting kit. </p>
Product capacity	Maximum load: With a span up to 1000 mm: 210 kg With a span up to 1300 mm: 150 kg.
Materials	Basic material: Aluminium Surface material: Polyester lacquer Cover cap: Cyclopy plastic
Ergonomy	The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.



PRESSALIT[®]

Product	PLUS anglehandrail section 400 x 154 mm, incl. wall rosette
Item number	RT341112
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.
Cleaning	The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.



PRESSALIT®









Product	PLUS anglehandrail section 400 x 154 mm, incl. wall rosette
Item number	RT341112

Installation in different wall types

	Concrete >B25 V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	Solid Brick >= Mz12 V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	Solid Sand Lime Brick >= Hlz12 V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	Aerated Concrete P4 V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6. To be ordered separately.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8615 - Mounting kit, 4 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.	



PRESSALIT®

Product Item number	PLUS anglehandrail section 400 x 154 mm, incl. wall rosette RT341112		
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.		
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm) Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.		
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.		

pressalit.com