



PRESSALIT®

Product Item number	PLUS angle grab bar section 15.8" x 6", incl. wall rosette RT341112
Color	VVS:777569412 NRF:6311273 EAN:5708590318943 NBS:N13:436 Anthracite gray
Product description	<p>PLUS angle grab bar tube, left, 90° angle with one wall rosette and connecting unit male joint. 15.8" x 6", diameter 1.3". Requires other grab bar elements for installation. <i>Please enquire for special grab bar solutions.</i> Please note that RT360 PLUS grab bar wall mounting with strap must always be installed at all joints of tubes or every 47". Excl. mounting kit. See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p> <p>PLUS angle grab bar tube, left, 90° angle with one wall rosette and connecting unit male joint. 15.8" x 6", diameter 1.3". Requires other grab bar elements for installation. <i>Please enquire for special grab bar solutions.</i> Please note that RT360 PLUS grab bar wall mounting with strap must always be installed at all joints of tubes or every 47". Materials: Powder-coated aluminium and plastics. Excl. mounting kit.</p>
Product capacity	Maximum load: With a span up to 39.4" : 460 lbs. With a span up to 51.2" : 330 lbs.
Materials	Core material: Aluminium Surface material: Polyester lacquer Cover cap: Cyclopy plastic
Ergonomy	The 1.3" diameter enables the rail to be held comfortably and firmly. The projection of 2" from the wall makes it easy to take hold of the rail.
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.



PRESSALIT[®]











Product	PLUS angle grab bar section 15.8" x 6", incl. wall rosette
Item number	RT341112
Cleaning	This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.



PRESSALIT®









Product	PLUS angle grab bar section 15.8" x 6", incl. wall rosette
Item number	RT341112

Mounting in different wall types

	Concrete >B25 V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	Solid Brick >= Mz12 V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	Solid Sand Lime Brick >= Hlz12 V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	Aerated Concrete P4 V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6, for aerated concrete. To be ordered separately.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.	



PRESSALIT®

Product Item number	PLUS angle grab bar section 15.8" x 6", incl. wall rosette RT341112		
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.		
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch) Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.		
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.		

pressalit.com

Pressalit A/S
 Pressalitvej 1
 DK-8680 Ry
 Tel.: +45 8788 8788
 Fax: +45 8788 8789
 E-mail: pressalit@pressalit.com

PRESSALIT®