



Product Item number	PLUS fitting with strap and joint RT361112
Color	VVS:777569612 NRF:6311282 EAN:5708590318981 NBS:N13:436 Anthracite gray
Product description	<p>PLUS grab bar wall mounting with strap and tube connector, male and female joint. For assembling tubes with diameter 1.3". Requires other grab bar elements for installation. <i>Please enquire for special grab bar solutions.</i> Excl. mounting kit. See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p> <p>PLUS grab bar wall mounting with strap and tube connector, male and female joint. For assembling tubes with diameter 1.3". Requires other grab bar elements for installation. <i>Please enquire for special grab bar solutions.</i> Materials: Plastics. Excl. mounting kit.</p>
Product capacity	Maximum load: With a span up to 39.4" : 460 lbs. With a span up to 51.2" : 330 lbs.
Materials	Cover cap: Cyclopy plastic Strap: Nylon (PA) Connecting unit: Polyphenylene oxide (PPO)
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.
Cleaning	This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.



PRESSALIT®









Product	PLUS fitting with strap and joint
Item number	RT361112

Mounting in different wall types

	Concrete >B25 V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	Solid Brick >= Mz12 V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	Solid Sand Lime Brick >= Hlz12 V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.	
	Aerated Concrete P4 V8665 - Mounting kit, 4 bolts M5 x 50 - plugs FTP K 6, for aerated concrete. To be ordered separately.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8615 - Mounting kit, 4 bolts Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.	



PRESSALIT®

Product Item number	PLUS fitting with strap and joint RT361112		
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.		
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch) Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.		
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.		

pressalit.com

Pressalit A/S
 Pressalitvej 1
 DK-8680 Ry
 Tel.: +45 8788 8788
 Fax: +45 8788 8789
 E-mail: pressalit@pressalit.com

PRESSALIT®