



PRESSALIT®

Product Item number	MATRIX ANGLE sink without overflow, left-facing R2043000
Color	VVS:636855000 NRF:6132511 EAN:5708590325132 HMI: 82617 NBS:N13:30,335 White
Product description	MATRIX is a series of sinks, most of them are designed by Pressalit. MATRIX SMALL and CURVE sinks fit onto PLUS, SELECT and VALUE sink brackets, whereas MATRIX MEDIUM and ANGLE are tailor made to fit specific brackets. MATRIX ANGLE vanity sink, 39.4" x 22.4" x 4.7", left-facing, with two integrated grab handles in the front, with tap hole diameter 1.4", without overflow, incl. drain fitting. The sink has raised edges, preventing water from running over the back or down the outer sides. Materials: Cultured marble with a high-polished, nonporous sanitary gel coating. Suitable for R2015 height adjustable sink supports.
Product capacity	440 lbs.
Materials	Cultured marble with a high-polished, nonporous sanitary gel coating.
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.



Product	MATRIX ANGLE sink without overflow, left-facing
Item number	R2043000
Cleaning	For cleaning the wash basin, use hot water and a mild soapy cleaning agent. Make sure that the product is wiped down with a soft rag wrung out in clear water immediately after cleaning. For disinfecting the wash basin, the following agents can be used: Sodium hydroxide 5% Acetic acid solution 10% Ethanol solution 70% Sodium hypochlorite 5%, active chlorine Sodium chloride 170g/l, diluted to 50%. Make sure that the product is wiped down with a soft rag wrung out in clear water immediately after disinfection. NB! Do not use abrasive cleaning agents, as this will cause damage to the surface of the wash basin.
Declaration of conformity	Declaration of Performance Compliance criteria according to EN 14688:2015. 4.1 Load resistance: stable, without cracks or deformations. 4.2 Draining of water: Water drained away completely. 4.3 Resistance to temperature changes: Without cracks, delaminations. 4.4 Resistance to chemicals and staining agents: - Sodium hydroxide 5% - without staining or deterioration; - Acetic acid solution 10% - without staining or deterioration; - Ethanol sol. 70% - without staining or deterioration; - Sodium hypochlorite 5% active chlorine - without staining or deterioration; - Sodium chloride 170g/l diluted to 50% - without staining or deterioration. 4.5 Surface stability / resistance to scratching: Do not use abrasives on the surface. 4.6 Cleanability: Smooth, non-absorbant surfaces. 4.7 Protection against overflowing: CL 00. 4.8 Durability: Product is considered durable.