




PRESSALIT®

Product Item number	Changing table, 800 x 1800 mm, electrically height adjustable, with sanitary appliances and standard mixer tap R8735000
Colour	VVS: 777630330 NRF: 7501987 EAN: 5708590333786 HMI: 105715 White
Product description	<p>Pressalit offers a wide range of daycare changing tables, both free-standing and wall-hung, in several sizes and models. The wall-hung tables are also available in versions where the worktop folds away, which are suitable for rooms with limited space. Of particular use to daycare facilities and kindergartens are the low start wall-hung changing tables, which can be lowered to a height that allows children to climb onto the worktop themselves.</p> <p>All types of daycare changing tables are available in versions with sanitary appliances and a choice of taps, with or without pull-out shower heads.</p> <p>Wallhung changing table, with sanitary appliances, 800 x 1800 mm. With electric motor and transformer, height adjustable from 650 mm - 1000 mm, with wired hand control. Laminate worktop with inset stainless steel sink, incl. lever operated mixer tap, feed/waste system and 2 wire baskets. Materials: Laminate and powder-lacquered steel. Excl. mounting kit.</p>
Adjustability	Height adjustable
Adjustment height	350 mm
Product capacity	Max load: 150 kg.
Speed upwards	Speed up mm: 14 mm/s Speed down mm: 14 mm/s
Noise level	48 dB





PRESSALIT®

Product	Changing table, 800 x 1800 mm, electrically height adjustable, with sanitary appliances and standard mixer tap
Item number	R8735000
Materials	Lifting unit and baskets: Powder-laquered steel. Worktop: Melamine. Waste pipe: Polyurethane, PVC and steel. The flexible waste pipe is very resistant to both chemical and physical influences. It is flame retardant and withstands temperatures from -30°C to +110°C.
Ergonomy	The smooth height adjustment ensures that it is always possible to set the table at an ergonomically correct height.
Features	Easy-to-clean surfaces ensure optimum hygiene. Underglued sink and tap.
Mains connection (V)	230
Actuator (motor)	2 x LA31 Deskline (Linak), 1500N, IPX1
Control box	CBD6 (Linak), IP20
Wired remote control	HB30 (Linak), IPX4
Power consumption (maximum load)	Power consumption by maximum load, watt: 96 W Power consumption by standby: 0,1 W
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.













PRESSALIT®

Product Item number	Changing table, 800 x 1800 mm, electrically height adjustable, with sanitary appliances and standard mixer tap R8735000
Cleaning	<p>Daycare changing tables The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p>
Declaration of conformity	<p>CE UK MASK-ROHS This product complies with the relevant requirements of:</p> <ul style="list-style-type: none">- Council Directive 2006/42/EC on machinery- Council Directive 2011/65/EC on RoHS. <p>For the UK: - The Supply of Machinery (Safety) Regulations 2008 - Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012</p>



Product	Changing table, 800 x 1800 mm, electrically height adjustable, with sanitary appliances and standard mixer tap
Item number	R8735000

Installation in different wall types

	<p>Concrete >B25</p> <p>V8608 - Mounting kit, 6 coach screws Ø10 x 70 - plugs SX12. To be ordered separately.</p>	
	<p>Solid Brick >= Mz12</p> <p>V8608 - Mounting kit, 6 coach screws Ø10 x 70 - plugs SX12. To be ordered separately.</p>	
	<p>Solid Sand Lime Brick >= Hlz12</p> <p>V8608 - Mounting kit, 6 coach screws Ø10 x 70 - plugs SX12. To be ordered separately.</p>	
	<p>Aerated Concrete P4</p> <p>V8658 - Mounting kit, 6 coach screws Ø10 x 70 - plugs GB14. To be ordered separately.</p>	
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</p> <p>V8608 - Mounting kit, 6 coach screws Ø10 x 70 - plugs SX12. NB! Plugs are not needed. To be ordered separately.</p>	



PRESSALIT®

Product Item number	Changing table, 800 x 1800 mm, electrically height adjustable, with sanitary appliances and standard mixer tap R8735000
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm) Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.

pressalit.com

Pressalit A/S
 Pressalitvej 1
 DK-8680 Ry
 Tel.: +45 8788 8788
 Fax: +45 8788 8789
 E-mail: pressalit@pressalit.com

PRESSALIT®