




# PRESSALIT®

<b>Product</b> <b>Item number</b>	Lift for worktop, electrically height adjustable RK1081-92
<b>Product description</b>	<p>EAN:5708590334592</p>  <p>The name INDIVO relates to the individual configuration of the products.</p> <p>Electric lift for freestanding worktop.  For worktops from 1400 - 2000 mm.  Height adjustable 300 mm.  Including 2 telescopic legs, longitudinal and cross braces and switch.  Pressalit recommends overhang of 200 mm at either end to allow ease of approach in wheel-chair.  Please state desired length when ordering.</p>
<b>Adjustability</b> <b>Adjustment height</b>  <b>Product capacity</b>  <b>Speed upwards</b>  <b>Noise level</b>	Height adjustable 300 mm  Maximum load (evenly distributed): 100 kg including worktop. Speed up mm: 20 mm/s Speed down mm: 20 mm/s  45 dB
<b>Materials</b>	Material: Telescopic leg: Aluminium, ABS plastic Cross braces: Aluminium Brackets: Steel Cable tray: ABS plastic Switches: ABS plastic Surface treatment: Brackets: Powder lacquered (grey RAL 9006)



<b>Product</b>	Lift for worktop, electrically height adjustable
<b>Item number</b>	RK1081-92
<b>Ergonomy</b>	<p>A freestanding electric Indivo solution is a flexible work or dining table, primarily intended for use in the kitchen.</p> <p>The height of the worktop can be quickly and easily adjusted to the given user or situation.</p> <p>A freestanding worktop can also be used in rooms in which the walls are not strong enough to support the wall-mounted models.</p>
<b>Features</b>	<p>Lift heights are adjusted via switches set in the edge or directly under the worktop. Operating switches can be placed anywhere.</p> <p>The design of the legs and feet make the table stable and secure, and ensure the lift causes minimal inconvenience to wheelchair users.</p> <p>The design of the lift makes it possible to use the worktop from all sides.</p> <p>Height adjustable over a range of 300 mm.</p> <p>Available for worktops of any length between 1400 mm and 3000 mm.</p>
<b>Actuator (motor)</b>	DB4 Deskline (Linak) 1000 N, IP22
<b>Control box</b>	CBD6 (Linak)
<b>Power consumption (maximum load)</b>	<p>Power consumption by maximum load, watt: 300 W</p> <p>Power consumption by standby: 2 W</p>
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.



# PRESSALIT®

<b>Product</b>	Lift for worktop, electrically height adjustable
<b>Item number</b>	RK1081-92
<b>Cleaning</b>	<p>INDIVO lift for kitchen worktop. The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p><b>DISINFECTANTS:</b> Clinimax Difficil-S Erisan OXY+</p> <p><b>NON-DISINFECTANTS:</b> Suma Star free D1 Taski 100 Taski 200</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p><b>DECALCIFICATION OF ALUMINUM PARTS:</b> Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts must be wiped over with a damp cloth wrung out in clear water.</p>

[pressalit.com](http://pressalit.com)

# PRESSALIT®