



Product	Changing table, 800 x 1400 mm, electrically height adjustable, with sanitary appliances and mixer tap with pull-out spout	
Item number	R8652000 VVS:777637220 NRF:7501969 EAN:5708590338316 HMI: 48880	
Colour	White	
Product description	<p>Freestanding changing table with sanitary appliances, 800 x 1400 mm.</p> <p>With electric motor and transformer, height adjustable from 650 mm - 1000 mm, with wired hand control.</p> <p>Molded worktop with integrated sink, incl. lever operated mixer tap, pull-out shower head, feed/waste system and 2 wire baskets.</p>	
Adjustability	Height adjustable	
Adjustment height	350 mm	
Product capacity	Max load: 75 kg.	
Speed, upwards	Speed up mm: 14 mm/s Speed down mm: 14 mm/s	
Noise level	48 dB	
Materials	<p>Lifting unit and baskets: Powder-laquered steel.</p> <p>Worktop: ABS with acrylic.</p> <p>Waste pipe: Polyurethane, PVC and steel. The flexible waste pipe is very resistant to both chemical and physical influences. It is flame retardant and withstands temperatures from -30°C to +110°C.</p>	
Ergonomy	The smooth height adjustment ensures that it is always possible to set the table at an ergonomically correct height.	
Features	Easy-to-clean surfaces ensure optimum hygiene. Integrated sink and tap with pull-out spout.	
Mains connection (V)	230	
Actuator (motor)	LA31 Deskline (Linak), 1500N, IPX1	
Control box	CBD6 (Linak), IP22	
Wired remote control	HB3 (Linak), IP66	





PRESSALIT®

Product	Changing table, 800 x 1400 mm, electrically height adjustable, with sanitary appliances and mixer tap with pull-out spout
Power consumption (maximum load)	Power consumption by maximum load: 96 W Power consumption by standby: 0,1 W
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.
Cleaning	<p>Changing table. The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p>
Declaration of conformity	This product complies with the requirements of Council Directive 2006/42/EC (of 17 May 2006) on machinery and the Council Directive 2011/65/EC on RoHS.



www.pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®