




Product Item number	Changing table, 800 x 1800 mm, electrically height adjustable, foldable R8673000
Colour Product description	<p>VVS: 777636130 NRF: 7501979 EAN: 5708590338408 HMI: 48575</p> <p>White</p> <p>Low start, wallhung, foldable changing table, 800 x 1800 mm. With electric motor and transformer, height adjustable from 300 mm - 1000 mm, with wired hand control. Materials: Worktop in laminate and powder-lacquered steel. Excl. fixing kit. See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p> 
Adjustability Adjustment height Product capacity Speed Noise level	<p>Height adjustable</p> <p>700 mm</p> <p>Max load: 75 kg.</p> <p>Speed up mm: 38 mm/s Speed down mm: 38 mm/s</p> <p>48 dB</p>
Materials Ergonomy Features Mains connection (V)	<p>Lifting unit: Powder-laquered steel. Worktop: Melamine.</p> <p>The smooth height adjustment ensures that it is always possible to set the table at an ergonomically correct height. The table descends to a very low position, which offers the advantage that toddlers can easily climb up and down themselves. Thereby unnecessary lifting is avoided.</p> <p>Easy-to-clean surfaces ensure optimum hygiene. The integrated gas cylinder enables the table to be folded easily against the wall when not in use to maximise floor space. Integrated safety system prevents entrapment.</p> <p>230</p>










Product Item number	Changing table, 800 x 1800 mm, electrically height adjustable, foldable R8673000
Actuator (motor) Control box Wired remote control Power consumption (maximum load)	LA31 Deskline (Linak), 3500N, IPX1 CBD6 (Linak), IP22 HB3 (Linak), IP66 Power consumption by maximum load: 96 W Power consumption by standby: 0,1 W
Warranty Cleaning	<p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.</p> <p>Changing table. The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p>
Declaration of conformity	This product complies with the requirements of Council Directive 2006/42/EC (of 17 May 2006) on machinery and the Council Directive 2011/65/EC on RoHS.










Product	Changing table, 800 x 1800 mm, electrically height adjustable, foldable
Item number	R8673000

Installation in different wall types

	Concrete >B25 V8608 - Fixing kit, 6 coach screws Ø10 x 70 - plugs SX12. To be ordered separately.
	Solid Brick >= Mz12 V8608 - Fixing kit, 6 coach screws Ø10 x 70 - plugs SX12. To be ordered separately.
	Solid Sand Lime Brick >= Hlz12 V8608 - Fixing kit, 6 coach screws Ø10 x 70 - plugs SX12. To be ordered separately.
	Aerated Concrete P4 V8658 - Fixing kit, 6 coach screws Ø10 x 70 - plugs GB14. To be ordered separately.
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8608 - Fixing kit, 6 coach screws Ø10 x 70 - plugs SX12. NB! Plugs are not needed. To be ordered separately.





Product Item number	Changing table, 800 x 1800 mm, electrically height adjustable, foldable R8673000	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm) Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.	
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.	