



<b>Product</b>	Changing table, 800 x 1400 mm, electrically height adjustable, with sanitary appliances and mixer tap with pull-out spout	
<b>Item number</b>	R8682000 VVS:777636220 NRF:7501981 EAN:5708590338415 HMI: 48564	
<b>Colour</b>	White	
<b>Product description</b>	<p>Low start, wallhung changing table, with sanitary appliances, 800 x 1400 mm. With electric motor and transformer, height adjustable from 300 mm - 1000 mm, with wired hand control and safety stop function. Molded worktop with integrated sink, incl. lever operated mixer tap, pull-out shower head, feed/waste system and 2 wire baskets.</p> <p>Excl. fixing kit. See Technical datasheet (pdf) for information on fixings suitable for various wall types.</p>	
<b>Adjustability</b>	Height adjustable	
<b>Adjustment height</b>	700 mm	
<b>Product capacity</b>	Max load: 75 kg.	
<b>Speed, upwards</b>	Speed up mm: 38 mm/s	
<b>Speed, downwards</b>	Speed down mm: 38 mm/s	
<b>Noise level</b>	48 dB	
<b>Materials</b>	Lifting unit and baskets: Powder-laquered steel. Worktop: ABS with acrylic.	
<b>Ergonomy</b>	<p>The smooth height adjustment ensures that it is always possible to set the table at an ergonomically correct height.</p> <p>The table descends to a very low position, which offers the advantage that toddlers can easily climb up and down themselves. Thereby unnecessary lifting is avoided.</p>	
<b>Features</b>	<p>Easy-to-clean surfaces ensure optimum hygiene.</p> <p>Integrated sink and tap with pull-out spout.</p> <p>Integrated safety system prevents entrapment.</p>	
<b>Mains connection (V)</b>	230	
<b>Actuator (motor)</b>	LA31 Deskline (Linak), 2500N, IPX1	










<b>Product</b>	Changing table, 800 x 1400 mm, electrically height adjustable, with sanitary appliances and mixer tap with pull-out spout
<b>Control box</b>	CBD6 (Linak), IP22
<b>Wired remote control</b>	HB3 (Linak), IP66
<b>Power consumption (maximum load)</b>	Power consumption by maximum load: 96 W Power consumption by standby: 0,1 W
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.
<b>Cleaning</b>	<p>Changing table. The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p>
<b>Declaration of conformity</b>	This product complies with the requirements of Council Directive 2006/42/EC (of 17 May 2006) on machinery and the Council Directive 2011/65/EC on RoHS.





<b>Product</b>	Changing table, 800 x 1400 mm, electrically height adjustable, with sanitary appliances and mixer tap with pull-out spout
----------------	---







## Installation in different wall types

	<b>Concrete &gt;B25</b> V8608 - Fixing kit, 6 coach screws Ø10 x 70 - plugs SX12. To be ordered separately.
	<b>Solid Brick &gt;= Mz12</b> V8608 - Fixing kit, 6 coach screws Ø10 x 70 - plugs SX12. To be ordered separately.
	<b>Solid Sand Lime Brick &gt;= Hlz12</b> V8608 - Fixing kit, 6 coach screws Ø10 x 70 - plugs SX12. To be ordered separately.
	<b>Aerated Concrete P4</b> V8658 - Fixing kit, 6 coach screws Ø10 x 70 - plugs GB14. To be ordered separately.
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b> V8608 - Fixing kit, 6 coach screws Ø10 x 70 - plugs SX12. NB! Plugs are not needed. To be ordered separately.





# PRESSALIT®

Product	Changing table, 800 x 1400 mm, electrically height adjustable, with sanitary appliances and mixer tap with pull-out spout	
	<p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b></p> <p>Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.</p>	<p>fischer KD 8    snaptight    wingit</p> 
	<p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</b></p> <p>Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.</p>	<p>fischer KD 8    snaptight    wingit</p> 
	<p><b>Drywall (2 x 12,5 mm) water-resistant</b></p> <p>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.</p>	



[www.pressalit.com](http://www.pressalit.com)

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®