




<p>Product Item number</p>	<p>MATRIX manual sink bracket, height adjustable R4826000</p>
<p>Color Product description</p>	<p>EAN:5708590349688 FDA:ILW/D142473</p>  <p>White</p> <p>MATRIX brackets are tailor made for MATRIX sinks. They are available in electrically and manually height adjustable versions, as well as fixed versions, all of them with a hygienic cover to conceal the plumbing installations.</p> <p>MATRIX sink bracket, wall-mounted, with white installation cover and incl. concealed flexible feed/waste system. Manually height adjustable by 7.9" with crank handle. Incl. mounting bolts for sink (Can only be used with MATRIX MEDIUM sinks, R2120/R2121). Materials: Powder-coated stainless steel and PMMA. Excl. mounting kit. We recommend T4679 plumbing kit with 0.4" compatible adaptor.</p>
<p>Adjustability Adjustment height Product capacity</p>	<p>Height adjustable 7,88 inch</p> <p>Maximum load: 331 lbs. Suitable for sinks weighing no more than 55 lbs. When the sink is loaded with 331 lbs, each wall fastener will be carrying 132 lbs. <i>Sink brackets need to be able to carry the weight of the sink, as well as support the weight of the person who is leaning against the sink or who is using the sink to rise from seated position.</i> Neither sink nor sink bracket are intended to carry the full body weight of a person, and the test methods applicable to sink brackets reflect this: ISO 17966 prescribes a static test on the front edge of the sink at 75% of maximum user weight, i.e. when the maximum load on a sink bracket is given as 331 lbs and the wash basin weighs 55 lbs, it is – according to ISO 17966 – the equivalent of a user weighing 368 lbs leaning on the front edge of the wash basin.</p>



Product	MATRIX manual sink bracket, height adjustable
Item number	R4826000
Speed up	Speed up: 0,46 inch/s Speed down: 0,46 inch/s
Noise level	48 dB
Materials	Powder-coated stainless steel and PMMA.
Power consumption (maximum load)	Power consumption by standby: 1,5 W
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.
Cleaning	<p>This product should be cleaned with hot water or a mild cleaning solution. Do not use corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>For surface disinfection, chlorine-based disinfectants may be used according to the product specification and safety precautions for these products.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: CaviCide</p>
Declaration of conformity	This product is solely intended for the US and Canada, and has no EU declaration of conformity.









Product	MATRIX manual sink bracket, height adjustable
Item number	R4826000

Mounting in different wall types

	<p>Concrete >B25</p> <p>V8605 - Mounting kit, 4 lag bolts Ø10 x 70, plugs SX12, with grey covers. To be ordered separately.</p>	
	<p>Solid Brick >= Mz12</p> <p>V8605 - Mounting kit, 4 lag bolts Ø10 x 70, plugs SX12, with grey covers. To be ordered separately.</p>	
	<p>Solid Sand Lime Brick >= Hlz12</p> <p>V8605 - Mounting kit, 4 lag bolts Ø10 x 70, plugs SX12, with grey covers. To be ordered separately.</p>	
	<p>Aerated Concrete P4</p> <p>V8655 - Mounting kit, 4 lag bolts Ø10 x 70, plugs GB14, with grey covers. To be ordered separately.</p>	
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</p> <p>V8605 - Mounting kit, 4 lag bolts Ø10 x 70, plugs SX12, with white covers. NB! Plugs are not needed. To be ordered separately.</p>	



<p>Product Item number</p>	<p>MATRIX manual sink bracket, height adjustable R4826000</p>	
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or Wingt anchors or similar.</p>	
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch) Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or Wingt anchors or similar.</p>	
	<p>Drywall (2 x 12,5 mm) water-resistant Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or Wingt anchors or similar.</p>	

It is the responsibility of the installer to ensure that suitable wall fasteners are used.