




# PRESSALIT®

<b>Product</b> <b>Item number</b>	PLUS shower seat 450, manually height adjustable R7424026
<b>Colour</b>	EAN: 5708590359656 HMI: 124341 FDA: INN/D135865  Orange
<b>Product description</b>	 <p>PLUS shower seats are offered in a number of colours. They are available as both fixed height, electrically adjustable and manually adjustable, with and without aperture, and with an option of back and armrests. They are suitable for wall-mounting or for fitting to Pressalit PLUS wall tracks.</p> <p>PLUS shower seat 450, with backrest. Manually height adjustable by 380 mm, without the use of tools. The seat is foldable.          Materials: Comfortable polyurethane foam over a plywood core, fitted to an aluminium profile.          Excl. mounting kit.  <i>Replaces R7420</i></p>
<b>Adjustability</b> <b>Adjustment height</b>  <b>Product capacity</b>	Height adjustable 380 mm  Maximum user mass: 200 kg. When the seat is loaded with 200 kg, each wall fastener is loaded with 24 kg.  <i>The seat has been tested statically with safety factor 1.5, which is a requirement according to the applied assistive products standards.</i>
<b>Materials</b>  <b>Ergonomy</b>	The shower seat is made of polyurethane (PU) foam with a plywood core and this is covered with an in-mould coated surface that is protected using a clear PU lacquer. The backrest is made of polyurethane (PU) foam protected using a clear PU lacquer. Internal components and fasteners are primarily made of stainless steel. The hinge barrel is capped with ABS.  Ergonomically designed seat - contact surface are 450 x 437 mm. Soft and slip-resistant material that has a warm feel.













# PRESSALIT®

<b>Product</b>	PLUS shower seat 450, manually height adjustable
<b>Item number</b>	R7424026
<b>Features</b>	The seat can fold up when not in use or to maximise floor space. The seat and backrest can be adjusted simultaneously thanks to a safe and easy click system.
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.
<b>Cleaning</b>	<p>PLUS shower seat.</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>Important: Polyurethane surfaces of PLUS shower seats and PLUS backrests contains an antibacterial surface, which will be compromised if cleaned with anything other than soap and water.</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p><b>DECALCIFICATION OF ALUMINUM PARTS:</b> Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts must be wiped over with a damp cloth wrung out in clear water.</p>
<b>Declaration of conformity</b>	CE MDR This product is in compliance with all relevant requirements of: - Regulation (EU) 2017/745 on medical devices.















<b>Product</b>	PLUS shower seat 450, manually height adjustable
<b>Item number</b>	R7424026

## Installation in different wall types

	<p><b>Concrete &gt;B25</b></p> <p>V8612 - Mounting kit, 10 coach screws Ø8 x 70, plugs SX10. To be ordered separately.</p> 
	<p><b>Solid Brick &gt;= Mz12</b></p> <p>V8612 - Mounting kit, 10 coach screws Ø8 x 70, plugs SX10. To be ordered separately.</p> 
	<p><b>Solid Sand Lime Brick &gt;= Hlz12</b></p> <p>V8612 - Mounting kit, 10 coach screws Ø8 x 70, plugs SX10. To be ordered separately.</p> 
	<p><b>Aerated Concrete P4</b></p> <p>V8662 - Mounting kit, 10 countersunk bolts M8 x 35, plugs FTP M 8. To be ordered separately.</p> 
	<p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b></p> <p>V8612 - Mounting kit, 10 coach screws Ø8 x 70, plugs SX10. NB! Plugs are not needed. To be ordered separately.</p> 



# PRESSALIT®

<b>Product</b> <b>Item number</b>	PLUS shower seat 450, manually height adjustable R7424026		
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b> Wall fasteners (10 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.	  	
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</b> Wall fasteners (10 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.	  	
	<b>Drywall (2 x 12,5 mm) water-resistant</b> Wall fasteners (10 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.	  	

pressalit.com

Pressalit A/S  
 Pressalitvej 1  
 DK-8680 Ry  
 Tel.: +45 8788 8788  
 Fax: +45 8788 8789  
 E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®