




PRESSALIT®

Product Item number	Flexible feed and waste system 36"/36" R2087
Product description	<p>EAN: 5708590360461</p>  <p>The flexible feed and waste systems are needed to ensure the flow of water to and from the height adjustable sink brackets.</p> <p>Flexible feed/waste system. Feed pipes: 36", waste pipe: 36". tap supply line braided stainless steel, with 3/8". OD x 1/2". IPS x 16". Flexible waste pipe, dia. 1.26".</p>
Materials	<p>The feed pipes are made from SPX plastic, braided with stainless steel. The connecting nuts are 3/8" and made from brass with 3/8" copper pipe. The waste pipe is flexible, corrugated white PVC with a diameter of 1.3". We do not recommend flushing the waste hose with formaldehyde. The elbow with removable connector is made from PP (polypropylene) with a seal of TPE (thermoplastic elastomer). Maximum temperatures of use are 176°F (continuous use) and 194°F (temporary use). PP is very resistant to water, damp and most organic solvents. The seal is made from EPDM – Temperature of use from -58°F - +248°F/305°F EPDM is particularly resistant to ozone and weather. Good resistance to heat and cold and to most chemicals – but poor resistance to petroleum products and solvents.</p>
Ergonomy	<p>To maximize product flexibility, it is important that the plumbing installation is correctly positioned and does not obstruct movement. The waste hose can be shortened on site to fit the installation.</p>
Warranty	<p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.</p>
Cleaning	<p>When cleaning the sink, it is recommended to do one flush through the waste hose with 122-140 degrees hot water in order to prevent build-up of soap residues inside the hose. Ensure that the hose is stretched out during this flushing.</p>



PRESSALIT®

Product	Flexible feed and waste system 36"/36"
Item number	R2087

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®