



PRESSALIT®

Product Item number	CT 4000 change table, manually foldable, electrically height adjustable R8594572000
Color	EAN:5708590358154 FDA:INQ/D124319 White
Product description	Pressalit offers a variety of mobile and wall-hung, height-adjustable and fixed height shower and changing tables of high quality. They are designed to provide a stable platform for showering and changing adults and children with reduced mobility. These tables can be used in schools, institutions, hospitals and private homes and are all designed to be durable, comfortable and easy to clean. The design and flexibility of the tables ensures optimal working conditions for the carer as well as a high level of comfort and safety for the user. The CT 4000 series has been designed for public changing facilities and schools. CT 4000 change table, manually foldable. Electrically height adjustable 27.6"; from 11.8" - 39.4", with buttons placed in table front. Incl. safety rail, body belt and wired remote control. Lying surface 32" x 72", in compact laminate. Outer measurements 39.7 x 72". Excl. mounting kit.
Adjustability Adjustment height Product capacity Speed up Noise level	Height adjustable 27,58 inch Maximum user weight (MUM): 500 lbs. Maximum load (SWL): 511 lbs. (User weight + accessories) When the table is loaded with 500 lbs, each mounting bolt supports 83 lbs. <i>This product has been tested statically with a load of 1279 lbs as the IEC 60601-1 standard requires testing with a safety factor 2.5.</i> Speed up: 0,59 inch/s Speed down: 0,79 inch/s 48 dB








PRESSALIT®

Product Item number	CT 4000 change table, manually foldable, electrically height adjustable R8594572000
Materials Ergonomy Mains connection (V) Power consumption (maximum load)	Powder-laquered stainless steel, lying surface in compact laminate. The ergonomically designed safety rail has a practical lower central section, which provides better access and work environment for the carer while transferring, changing and dressing the user. Easy to clean, smooth contact surfaces which do not collect dirt and bacteria. 120 Power consumption by maximum load: 312 W Power consumption by standby: 2 W
Warranty Cleaning Declaration of conformity	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date. This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged. The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate. This product is solely intended for the US and Canada, and has no EU declaration of conformity.





Product	CT 4000 change table, manually foldable, electrically height adjustable
Item number	R8594572000

Mounting in different wall types

	Concrete >B25 V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. To be ordered separately.	
	Solid Brick >= Mz12 V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. To be ordered separately.	
	Solid Sand Lime Brick >= Hlz12 V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. To be ordered separately.	
	Aerated Concrete P4 V8658 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs GB14. To be ordered separately.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. NB! Plugs are not needed. To be ordered separately.	



PRESSALIT®

Product Item number	CT 4000 change table, manually foldable, electrically height adjustable R8594572000		
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.		
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch) Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.		
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.		

It is the responsibility of the installer to ensure that suitable wall fasteners are used.

pressalit.com