




PRESSALIT®

Product Item number	<p>MATRIX powered sink bracket, height adjustable</p> <p>R4828000</p>
Color	<p>EAN: 5708590365565</p> <p>FDA: ILW/D142473</p> <p>White</p> 
Product description	<p>MATRIX brackets are tailor made for MATRIX sinks. They are available in electrically and manually height adjustable and sideways adjustable versions, as well as fixed versions, all of them with a hygienic cover to conceal the plumbing installations.</p> <p>MATRIX sink bracket, wall-mounted, with white installation cover and incl. flexible feed/waste system. Electrically height adjustable by 7.9" with operation buttons in front edge of sink. Incl. mounting bolts for sink (Can only be used with MATRIX MEDIUM sinks, R2122/R2123). Materials: Powder-coated stainless steel and PMMA. Excl. mounting kit. We recommend T4679 plumbing kit with 0.4" compatible adaptor.</p>
Adjustability	<p>Height adjustable</p>
Adjustment height	<p>7,88 inch</p>
Product capacity	<p>Maximum user weight (MUM): 368 lbs. Maximum load: 331 lbs. Suitable for sinks weighing no more than 55 lbs. When the sink is loaded with 331 lbs, each wall fastener will be carrying 132 lbs. <i>Sink brackets need to be able to carry the weight of the sink, as well as support the weight of the person who is leaning against the sink or who is using the sink to rise from seated position.</i> <i>Neither sink nor sink bracket are intended to carry the full body weight of a person, and the test methods applicable to sink brackets reflect this: ISO 17966 prescribes a static test on the front edge of the sink at 75% of maximum user weight, i.e. when the maximum load on a sink bracket is given as 331 lbs and the wash basin weighs 55 lbs, it is – according to ISO 17966 – the equivalent of a user weighing 368 lbs leaning on the front edge of the wash basin.</i></p>



PRESSALIT®

Product	MATRIX powered sink bracket, height adjustable
Item number	R4828000
Speed up	Speed up: 0,46 inch/s Speed down: 0,46 inch/s
Noise level	48 dB
Materials	Powder-coated stainless steel and PMMA.
Mains connection (V)	120
Actuator (motor)	LA31 Careline (Linak), 1500N, IPX6
Control box	CB9 Careline (Linak), IPX6
Power consumption (maximum load)	Power consumption by maximum load: 70 W Power consumption by standby: 1,5 W
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.













PRESSALIT®

Product	MATRIX powered sink bracket, height adjustable
Item number	R4828000
Cleaning	<p>This product should be cleaned with hot water or a mild cleaning solution. Do not use corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>For surface disinfection, chlorine-based disinfectants may be used according to the product specification and safety precautions for these products.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättspit 70%</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p>
Declaration of conformity	This product is solely intended for the US and Canada, and has no EU declaration of conformity.












Product	MATRIX powered sink bracket, height adjustable
Item number	R4828000

Mounting in different wall types

	Concrete >B25 V8605 - Mounting kit, 4 lag bolts Ø10 x 70, plugs SX12, with grey covers. To be ordered separately.	
	Solid Brick >= Mz12 V8605 - Mounting kit, 4 lag bolts Ø10 x 70, plugs SX12, with grey covers. To be ordered separately.	
	Solid Sand Lime Brick >= Hlz12 V8605 - Mounting kit, 4 lag bolts Ø10 x 70, plugs SX12, with grey covers. To be ordered separately.	
	Aerated Concrete P4 V8655 - Mounting kit, 4 lag bolts Ø10 x 70, plugs GB14, with grey covers. To be ordered separately.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8605 - Mounting kit, 4 lag bolts Ø10 x 70, plugs SX12, with white covers. NB! Plugs are not needed. To be ordered separately.	



PRESSALIT®

Product Item number	MATRIX powered sink bracket, height adjustable R4828000		
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.		
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch) Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.		
	Drywall (2 x 12,5 mm) water-resistant Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.		

It is the responsibility of the installer to ensure that suitable wall fasteners are used.

pressalit.com

Pressalit A/S
 Pressalitvej 1
 DK-8680 Ry
 Tel.: +45 8788 8788
 Fax: +45 8788 8789
 E-mail: pressalit@pressalit.com

PRESSALIT®