




PRESSALIT®

Product Item number	Changing table, 31.5" x 55.1", electrically height adjustable, foldable R8922000
Color	EAN:5708590367187 White
Product description	 Pressalit offers a wide variety of changing tables designed for use in daycare facilities. The tables are available in several sizes and models, either free standing or wall-hung. The fold away feature in wall-hung tables is useful where space is limited. The wall-hang tables with low start are essential for daycare or preschool facilities. Even toddlers can climb onto the table themselves, without the staff lifting them. Changing table, wall-mounted, foldable, 31.5" x 55.1". With motor and transformer, height adjustable from 25.6" - 39.4", with hand control. Materials: Molded worktop in ABS plastics, synthetic acrylic and powder-lacquered steel. Excl. fixing kit.
Adjustability	Height adjustable
Adjustment height	13,79 inch
Product capacity	Max load: 165 lbs.
Speed up	Speed up: 0,55 inch/s Speed down: 0,55 inch/s
Noise level	48 dB
Materials	Lifting unit: Powder-coated steel. Countertop: ABS with acrylic.
Ergonomy	The smooth height adjustment ensures that it is always possible to set the table at an ergonomically correct height.
Features	Easy-to-clean surfaces ensure optimum hygiene. The integrated pneumatic cylinder enables the table to be folded easily against the wall when not in use to maximize floor space.



PRESSALIT®






Product Item number	Changing table, 31.5" x 55.1", electrically height adjustable, foldable R8922000
Mains connection (V) Actuator (motor) Control box Wired remote control Power consumption (maximum load)	120 LA31 Deskline (Linak), 1500N, IPX1 CBD6 (Linak), IP20 HB30 (Linak), IPX4 Power consumption by maximum load: 96 W Power consumption by standby: 0,1 W
Warranty Cleaning	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date. This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged. The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container. DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70% NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.
Declaration of conformity	This product is solely intended for the US and Canada, and has no EU declaration of conformity.



PRESSALIT®





Product	Changing table, 31.5" x 55.1", electrically height adjustable, foldable
Item number	R8922000

Mounting in different wall types

	Concrete >B25 V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. To be ordered separately.	
	Solid Brick >= Mz12 V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. To be ordered separately.	
	Solid Sand Lime Brick >= Hlz12 V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. To be ordered separately.	
	Aerated Concrete P4 V8658 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs GB14. To be ordered separately.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12. NB! Plugs are not needed. To be ordered separately.	



PRESSALIT®

Product Item number	Changing table, 31.5" x 55.1", electrically height adjustable, foldable R8922000		
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.	  	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch) Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.	  	
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.		

pressalit.com