




# PRESSALIT®

<b>Product</b> <b>Item number</b>	Changing table, 31.5" x 35.4", electrically height adjustable R8941000
<b>Color</b>	EAN:5708590367194  White
<b>Product description</b>	<p>Pressalit offers a wide variety of changing tables designed for use in daycare facilities. The tables are available in several sizes and models, either free standing or wall-hung. The fold away feature in wall-hung tables is useful where space is limited. The wall-hung tables with low start are essential for daycare or preschool facilities. Even toddlers can climb onto the table themselves, without the staff lifting them.</p> <p>Changing table, freestanding, 31.5" x 35.4".          With motor and transformer, height adjustable from 25.6" - 39.4", with hand control.          Molded worktop, incl. 2 wire baskets.          Materials: ABS plastics, synthetic acrylic and powder-lacquered steel.</p>
<b>Adjustability</b> <b>Adjustment height</b> <b>Product capacity</b> <b>Speed up</b> <b>Noise level</b>	Height adjustable 13,79 inch Max load: 165 lbs. Speed up: 0,55 inch/s Speed down: 0,55 inch/s 48 dB
<b>Materials</b> <b>Ergonomy</b> <b>Features</b> <b>Mains connection (V)</b>	Lifting unit and baskets: Powder-coated steel. Countertop: ABS with acrylic. The smooth height adjustment ensures that it is always possible to set the table at an ergonomically correct height. Easy-to-clean surfaces ensure optimum hygiene. 120





<b>Product</b> <b>Item number</b>	Changing table, 31.5" x 35.4", electrically height adjustable R8941000
<b>Actuator (motor)</b>  <b>Control box</b>  <b>Wired remote control</b>  <b>Power consumption (maximum load)</b>	LA31 Deskline (Linak), 1500N, IPX1  CBD6 (Linak), IP20  HB30 (Linak), IPX4  Power consumption by maximum load: 96 W Power consumption by standby: 0,1 W
<b>Warranty</b>   <b>Cleaning</b>	<p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.</p> <p>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS:          Clinimax Difficil-S          Erisan OXY+          Sprit (husholdningssprit)          Suma Bac D10          Virkon          Rodalon Desinfektionsspray          Lysoformin Spezial          CaviCide          Sufanios Premium          Tvättspnit 70%</p> <p>NON-DISINFECTANTS:          Suma Star free D1          Taski 100          Taski 200          Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p>
<b>Declaration of conformity</b>	This product is solely intended for the US and Canada, and has no EU declaration of conformity.



# PRESSALIT®

<b>Product</b>	Changing table, 31.5" x 35.4", electrically height adjustable
<b>Item number</b>	R8941000

---

[pressalit.com](http://pressalit.com)

---

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®