




# PRESSALIT®

|  |  |
|--|--|
| <b>Product</b><br><b>Item number</b>   | Child changing table, 31.5" x 35.4", electrically height adjustable<br>R8961000  |
| <b>Color</b><br><br><b>Product description</b>   | <p>EAN:5708590367224</p> <p>White</p>  <p>Pressalit offers a wide variety of changing tables designed for use in daycare facilities. The tables are available in several sizes and models, either free standing or wall-hung. The fold away feature in wall-hung tables is useful where space is limited. The wall-hung tables with low start are essential for daycare or preschool facilities. Even toddlers can climb onto the table themselves, without the staff lifting them.</p> <p>Changing table, wall-mounted, low start, 31.5" x 35.4".<br/> With motor and transformer, height adjustable from 11.8" - 39.4", with hand control and safety stop function.<br/> Molded worktop, incl. 2 wire baskets.<br/> Materials: ABS plastics, synthetic acrylic and powder-lacquered steel.<br/> Excl. fixing kit.</p> |
| <b>Adjustability</b><br><b>Adjustment height</b><br><br><b>Product capacity</b><br><b>Speed up</b><br><br><b>Noise level</b> | Height adjustable<br>27,58 inch<br><br>Max load: 165 lbs.<br>Speed up: 1,5 inch/s<br>Speed down: 1,5 inch/s<br>48 dB   |
| <b>Materials</b><br><br><b>Ergonomy</b>  | <p>Lifting unit and baskets: Powder-laquered steel.<br/> Countertop: ABS with acrylic.</p> <p>The smooth height adjustment ensures that it is always possible to set the table at an ergonomically correct height.<br/> The table descends to a very low position, which offers the advantage that toddlers can easily climb up and down themselves. Thereby unnecessary lifting is avoided.</p>   |



|   |  |
|---|--|
| <b>Product</b><br><b>Item number</b>  | Child changing table, 31.5" x 35.4", electrically height adjustable<br>R8961000  |
| <b>Features</b><br><br><b>Mains connection (V)</b><br><br><b>Actuator (motor)</b><br><br><b>Control box</b><br><br><b>Wired remote control</b><br><br><b>Power consumption (maximum load)</b> | Easy-to-clean surfaces ensure optimum hygiene.<br>Integrated safety system prevents entrapment.<br><br>120<br><br>LA31 Deskline (Linak), 2500N, IPX1<br><br>CBD6 (Linak), IP20<br><br>HB30 (Linak), IPX4<br><br>Power consumption by maximum load: 96 W<br>Power consumption by standby: 0,1 W   |
| <b>Warranty</b><br><br><b>Cleaning</b>  | <p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.</p> <p>This product should be cleaned with hot water or a mild cleaning solution.<br/>Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS:<br/>Clinimax Difficil-S<br/>Erisan OXY+<br/>Sprit (husholdningssprit)<br/>Suma Bac D10<br/>Virkon<br/>Rodalon Desinfektionsspray<br/>Lysoformin Spezial<br/>CaviCide<br/>Sufanios Premium<br/>Tvättsprit 70%</p> <p>NON-DISINFECTANTS:<br/>Suma Star free D1<br/>Taski 100<br/>Taski 200<br/>Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> |













PRESSALIT<sup>®</sup>

|                                  |   |
|----------------------------------|---|
| <b>Product</b>                   | Child changing table, 31.5" x 35.4", electrically height adjustable                             |
| <b>Item number</b>               | R8961000  |
| <b>Declaration of conformity</b> | This product is solely intended for the US and Canada, and has no EU declaration of conformity. |











|                    |   |
|--------------------|---|
| <b>Product</b>     | Child changing table, 31.5" x 35.4", electrically height adjustable |
| <b>Item number</b> | R8961000  |

## Mounting in different wall types

|   |  |   |
|---|--|---|
|    | <p><b>Concrete &gt;B25</b></p> <p>V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12.<br/>To be ordered separately.</p>   |    |
|   | <p><b>Solid Brick &gt;= Mz12</b></p> <p>V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12.<br/>To be ordered separately.</p>   |   |
|  | <p><b>Solid Sand Lime Brick &gt;= Hlz12</b></p> <p>V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12.<br/>To be ordered separately.</p>  |  |
|  | <p><b>Aerated Concrete P4</b></p> <p>V8658 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs GB14.<br/>To be ordered separately.</p>  |  |
|  | <p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b></p> <p>V8608 - Mounting kit, 6 lag bolts Ø10 x 70 - plugs SX12.<br/>NB! Plugs are not needed.<br/>To be ordered separately.</p> |  |



# PRESSALIT®

| Product<br>Item number  | Child changing table, 31.5" x 35.4", electrically height adjustable<br>R8961000  |   |   |
|---|--|---|---|
|    | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b><br>Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.           |    |  |
|    | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch)</b><br>Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar. |    |  |
|  | <b>Drywall (2 x 12,5 mm) water-resistant</b><br>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.   |  |   |

pressalit.com

Pressalit A/S  
 Pressalitvej 1  
 DK-8680 Ry  
 Tel.: +45 8788 8788  
 Fax: +45 8788 8789  
 E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®