




Product Item number	VALUE II support arm, height adjustable R1119000
Colour	VVS:615891200 NRF:6191058 RSK:8487435 EAN:5708590367583 HMI: 123559 White
Product description	 <p>VALUE II support arm, wall-mounted, foldable, height adjustable 150 mm, projection 865 mm. The ergonomic design gives a secure and comfortable grip as well as a good sense of where the support arm ends. Incl. fixing bolts for brick wall. Plugs depend on wall type and must be ordered separately.</p> <p>VALUE II support arm, wall-mounted, foldable, height adjustable 150 mm, projection 865 mm. The ergonomic design gives a secure and comfortable grip as well as a good sense of where the support arm ends. Materials: Rilsan-coated steel, diecast aluminium, plastic. Incl. fixing bolts for brick wall. Plugs depend on wall type and must be ordered separately.</p>
Adjustability Adjustment height Product capacity	Height adjustable 150 mm Maximum load: 120 kg. When the support arm is loaded with 120 kg, each wall fastener is loaded with 86 kg.
Materials Ergonomy	<p>The support arm is manufactured from steel with a Rilsan coating, which is comfortable to the touch, easy to clean, and protects the metal against corrosion.</p> <p>Provides firm support when you are sitting, standing, or transferring to and from a toilet.</p> <p>Good, broad support surface for the hand and arm. The rounded form gives a firm and comfortable grip.</p>



PRESSALIT®











Product	VALUE II support arm, height adjustable
Item number	R1119000
Features	<p>The support arm can fold up when not in use or to make more space.</p> <p>Height adjustable 150 mm.</p>
Warranty	<p>Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.</p>
Cleaning	<p>VALUE support arms.</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>For surface disinfection, chlorine-based disinfectants may be used according to the product specification and safety precautions for these products.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Klorilli</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p>
Declaration of conformity	<p>CE MDR This product is in compliance with all relevant requirements of: - Regulation (EU) 2017/745 on medical devices.</p>



PRESSALIT®









Product	VALUE II support arm, height adjustable
Item number	R1119000

Installation in different wall types

	<p>Concrete >B25</p> <p>V8592 - 5 countersunk screws Ø10 x 80, with white screw covers are included. Plugs to be ordered separately.</p>	
	<p>Solid Brick >= Mz12</p> <p>V8592 - 5 countersunk screws Ø10 x 80, with white screw covers are included. Plugs to be ordered separately.</p>	
	<p>Solid Sand Lime Brick >= Hlz12</p> <p>V8592 - 5 countersunk screws Ø10 x 80, with white screw covers are included. Plugs to be ordered separately.</p>	
	<p>Aerated Concrete P4</p> <p>V8592 - 5 countersunk screws Ø10 x 80, with white screw covers are included. Plugs to be ordered separately.</p>	
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</p> <p>V8592 - 5 countersunk screws Ø10 x 80, with white screw covers are included. Plugs to be ordered separately.</p>	



PRESSALIT®

Product Item number	VALUE II support arm, height adjustable R1119000		
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (5 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.		
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm) Wall fasteners (5 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.		
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.		

It is the responsibility of the installer to ensure that suitable wall fasteners are used.

pressalit.com

Pressalit A/S
 Pressalitvej 1
 DK-8680 Ry
 Tel.: +45 8788 8788
 Fax: +45 8788 8789
 E-mail: pressalit@pressalit.com

PRESSALIT®