














PRESSALIT®

Product Item number	VALUE distance piece R1201000
Color	VVS:636859920 NRF:6132432 EAN:5708590369075 White
Product description	 <p>VALUE distance piece can be used where extra space below the sink is needed</p> <p>VALUE distance piece for sink, 23.5" x 4" x 4". Incl. fixing bolts for wash basin. Fits MATRIX SMALL and CURVE/CURVE II sinks. Excl. mounting kit.</p>
Product capacity	<p>Maximum load: 154 lbs. Suitable for sinks weighing no more than 49 lbs. When the sink is loaded with 154 lbs, each wall fastener will be carrying 412 lbs. <i>Sink brackets need to be able to carry the weight of the sink, as well as support the weight of the person who is leaning against the sink or who is using the sink to rise from seated position.</i></p> <p>Neither sink nor sink bracket are intended to carry the full body weight of a person, and the test methods applicable to sink brackets reflect this: ISO 17966 prescribes a static test on the front edge of the sink at 75% of maximum user weight, i.e. when the maximum load on a sink bracket is given as 154 lbs and the wash basin weighs 49 lbs, it is – according to ISO 17966 – the equivalent of a user weighing 141 lbs leaning on the front edge of the wash basin.</p>
Materials	Steel with a Rilsan coating, which is comfortable to the touch, easy to clean, and protects the metal against corrosion









Product	VALUE distance piece
Item number	R1201000

Mounting in different wall types

	<p>Concrete >B25</p> <p>V8605 - Mounting kit, 4 lag bolts Ø10 x 70, plugs SX12, with grey covers. To be ordered separately.</p>	
	<p>Solid Brick >= Mz12</p> <p>V8605 - Mounting kit, 4 lag bolts Ø10 x 70, plugs SX12, with grey covers. To be ordered separately.</p>	
	<p>Solid Sand Lime Brick >= Hlz12</p> <p>V8605 - Mounting kit, 4 lag bolts Ø10 x 70, plugs SX12, with grey covers. To be ordered separately.</p>	
	<p>Aerated Concrete P4</p> <p>V8655 - Mounting kit, 4 lag bolts Ø10 x 70, plugs GB14, with grey covers. To be ordered separately.</p>	
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</p> <p>V8605 - Mounting kit, 4 lag bolts Ø10 x 70, plugs SX12, with white covers. NB! Plugs are not needed. To be ordered separately.</p>	



Product Item number	VALUE distance piece R1201000
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Mounting in this wall type is not recommended - risk of fatal injury to persons and walls. 
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch) Mounting in this wall type is not recommended - risk of fatal injury to persons and walls. 
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls. 

It is the responsibility of the installer to ensure that suitable wall fasteners are used.