




PRESSALIT®

Product	Glasholder for wall, polished steel
Item number	Q10300
	EAN:5708590358826
	
Product description	
Materials	Stainless steel AISI 304, glass, mounting knot in brass
Cleaning	<p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.</p> <p>Subject to changes in the product range, technical changes and printing errors.</p>

www.pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®