



Product Item number	PLUS grab bar, corner shower combination, reversible left/right, 30" x 30" x 49.2" RT156112
Color	VVS: 777568682 NRF: 6317194 EAN: 5708590371146 HMI: 125873 Anthracite gray
Product description	PLUS grab bars are high-quality products and they can be combined in countless ways and they provide the final touch to furnishing a functional and flexible bathroom. A reliable solution with many different options, which can easily lay the grounds for increased independence. PLUS grab bar combination, 1.3", reversible right/left, A:30" x B:30" x C:49.2". Material: Powder-coated aluminium and plastic. Excl. mounting kit.
Product capacity	Maximum load: 440 lbs. When the grab bar is loaded with 440 lbs, each wall fastener is loaded with 123 lbs. <i>Grab bars are tested with a 1.5 safety factor in accordance with the requirements in ISO 17966:2016.</i>
Materials	Core material: Aluminium Surface material: Polyester lacquer Cover cap: Cycloy plastic Strap: Nylon (PA)
Ergonomy	The 1.3" diameter enables the rail to be held comfortably and firmly. The projection of 2" from the wall makes it easy to take hold of the rail.
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.








Product	PLUS grab bar, corner shower combination, reversible left/right, 30" x 30" x 49.2"
Item number	RT156112

Mounting in different wall types

	<p>Concrete >B25</p> <p>V8618 - Mounting kit, 16 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>	
	<p>Solid Brick >= Mz12</p> <p>V8618 - Mounting kit, 16 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>	
	<p>Solid Sand Lime Brick >= Hlz12</p> <p>V8618 - Mounting kit, 16 bolts Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>	
	<p>Aerated Concrete P4</p> <p>V8668 - Mounting kit, 16 bolts M5 x 50 - plugs FTP K 6, for aerated concrete. To be ordered separately.</p>	
	<p>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</p> <p>V8618 - Mounting kit, 16 bolts Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.</p>	



Product Item number	PLUS grab bar, corner shower combination, reversible left/right, 30" x 30" x 49.2" RT156112
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (16 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or Wingt anchors or similar. 
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch) Wall fasteners (16 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or Wingt anchors or similar. 
	Drywall (2 x 12,5 mm) water-resistant Mounting in this wall type is not recommended - risk of fatal injury to persons and walls. 