




PRESSALIT®

<b>Product</b> <b>Item number</b>	SELECT TL3 toilet lifter, electrical, for wall outlet R9143000
<b>Color</b>	EAN:5708590372778  White
<b>Product description</b>	 <p>SELECT TL3 and TL4 toilet lifters are developed with a clear focus on hygiene.  <b>Please contact Pressalit for more information about compatible toilet bowls for Pressalit SELECT toilet lifters</b></p> <p>SELECT TL3 toilet lifter, for wall outlet.          Incl. cUPC-approved cistern with dual flushing system preset at 0.8/1.6 gallons (can be changed to 0.5/1.1 gallons).          Manually height adjustable 8" with control panel on fold down grab bar.          Toilet pan, toilet seat and fold down grab bars (required for height adjustment) to be ordered separately.          Materials: Stainless steel and PMMA/ABS.          Excl. wall mounting kit.</p>
<b>Adjustability</b> <b>Adjustment height</b> <b>Product capacity</b> <b>Speed up</b> <b>Noise level</b>	Height adjustable 7,88 inch  Maximum user weight: 440 lbs. Maximum load: 518 lbs. (user weight + accessories). When the toilet lifter is loaded with 518 lbs, each wall fastener is loaded with 143 lbs. <i>The toilet lifter has been tested statically with 1320 lbs, which is a requirement according to the applied assistive products standards. Please note that most toilets compatible with this lifter have been tested up to 880 lbs.</i>  Speed up: 0,39 inch/s Speed down: 0,39 inch/s  48 dB
<b>Materials</b>	The toilet lifter is constructed of stainless steel, the cover fairing is made of PMMA/ABS plastics.



# PRESSALIT®











<b>Product</b>	SELECT TL3 toilet lifter, electrical, for wall outlet
<b>Item number</b>	R9143000
<b>Mains connection (V)</b>	230
<b>Power consumption (maximum load)</b>	Power consumption by maximum load: 70 W Power consumption by standby: 2 W
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.
<b>Cleaning</b>	<p>This product should be cleaned with hot water or a mild cleaning solution. Do not use corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>For surface disinfection, chlorine-based disinfectants may be used according to the product specification and safety precautions for these products.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p><b>DISINFECTANTS:</b> Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%</p> <p><b>NON-DISINFECTANTS:</b> Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p>
<b>Declaration of conformity</b>	This product is solely intended for the US and Canada, and has no EU declaration of conformity.



PRESSALIT®

<b>Product</b>	SELECT TL3 toilet lifter, electrical, for wall outlet
<b>Item number</b>	R9143000

## Mounting in different wall types

	<b>Concrete &gt;B25</b> V8605 - Mounting kit, 4 lag bolts Ø10 x 70, plugs SX12, with grey covers. To be ordered separately.	
	<b>Solid Brick &gt;= Mz12</b> V8605 - Mounting kit, 4 lag bolts Ø10 x 70, plugs SX12, with grey covers. To be ordered separately.	
	<b>Solid Sand Lime Brick &gt;= Hlz12</b> V8605 - Mounting kit, 4 lag bolts Ø10 x 70, plugs SX12, with grey covers. To be ordered separately.	
	<b>Aerated Concrete P4</b> V8655 - Mounting kit, 4 lag bolts Ø10 x 70, plugs GB14, with grey covers. To be ordered separately.	
	<b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b> V8605 - Mounting kit, 4 lag bolts Ø10 x 70, plugs SX12, with white covers. NB! Plugs are not needed. To be ordered separately.	



# PRESSALIT®

<b>Product</b> <b>Item number</b>	<b>SELECT TL3 toilet lifter, electrical, for wall outlet</b> <b>R9143000</b>
	<p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b></p> <p>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.</p>
	<p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch)</b></p> <p>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or WingIt anchors or similar.</p>
	<p><b>Drywall (2 x 12,5 mm) water-resistant</b></p> <p>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.</p>

pressalit.com

Pressalit A/S  
 Pressalitvej 1  
 DK-8680 Ry  
 Tel.: +45 8788 8788  
 Fax: +45 8788 8789  
 E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®