




# PRESSALIT®

|   |   |
|---|---|
| <b>Product</b><br><b>Item number</b>  | SELECT TL4 toilet lifter, electrical, for floor outlet<br>R9114000  |
| <b>Colour</b>   | VVS:617989700<br>NRF:6191188<br>EAN:5708590372891<br>HMI: 138238<br><br>White   |
| <b>Product description</b>  |  <p>SELECT TL3 and TL4 toilet lifters are developed with a clear focus on hygiene.</p> <p>SELECT TL4 toilet lifter, for floor outlet.<br/>         Incl. cistern with dual flushing system preset at 3/6 litres (can be changed to 2/4 litres).<br/>         Electrically height adjustable 200 mm with control panel on support arm.<br/>         Suitable for douche toilet or douche toilet seat. Toilet pan, toilet seat and support arms (required for height adjustment) to be ordered separately.<br/>         Materials: Stainless steel and PMMA/ABS.<br/>         Excl. wall mounting kit.</p> |
| <b>Adjustability</b><br><b>Adjustment height</b><br><br><b>Product capacity</b> | Height adjustable<br>200 mm<br><br>Maximum user weight: 200 kg.<br>Maximum load: 235 kg. (user weight + accessories).<br>When the toilet lifter is loaded with 235 kg, each wall fastener is loaded with 65 kg.<br><i>The toilet lifter has been tested statically with 600 kg, which is a requirement according to the applied assistive products standards. Please note that most toilet pans compatible with this lifter have been tested up to 400 kg.</i>  |
| <b>Speed upwards</b><br><br><b>Noise level</b>                                  | Speed up mm: 10 mm/s<br>Speed down mm: 10 mm/s<br><br>48 dB   |
| <b>Materials</b><br><br><b>Mains connection (V)</b>                             | The toilet lifter is constructed of stainless steel, the cover fairing is made of PMMA/ABS plastics.<br><br>230   |



# PRESSALIT®











|   |  |
|---|--|
| <b>Product</b>                          | SELECT TL4 toilet lifter, electrical, for floor outlet   |
| <b>Item number</b>                      | R9114000   |
| <b>Power consumption (maximum load)</b> | Power consumption by maximum load, watt: 70 W<br>Power consumption by standby: 2 W   |
| <b>Warranty</b>                         | Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.  |
| <b>Cleaning</b>                         | <p>SELECT TL3/TL4 toilet lifter.</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>For surface disinfection, chlorine-based disinfectants may be used according to the product specification and safety precautions for these products.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p><b>DISINFECTANTS:</b><br/>Clinimax Difficil-S<br/>Erisan OXY+<br/>Klorilli</p> <p><b>NON-DISINFECTANTS:</b><br/>Suma Star free D1<br/>Taski 100<br/>Taski 200</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> |
| <b>WEEE</b>                             | Please enquire of your local Pressalit subsidiary or distributor (in countries where there is no subsidiary) that will arrange for recycling of electronic waste in accordance with the WEEE directive.  |
| <b>Declaration of conformity</b>        | <p>CE UK MDR-MASK-RoHS This product is in compliance with all relevant requirements of:</p> <ul style="list-style-type: none"> <li>- Regulation (EU) 2017/745 on medical devices</li> <li>- Council Directive 2006/42/EC on machinery</li> <li>- Council Directive 2011/65/EC on RoHS. <b>For the UK:</b></li> <li>- Medical Device Regulation (MDR) 2002 on medical devices.</li> <li>- Supply of Machinery (Safety) Regulations 2008</li> <li>- Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012.</li> </ul>   |



PRESSALIT®











|                    |  |
|--------------------|--|
| <b>Product</b>     | SELECT TL4 toilet lifter, electrical, for floor outlet |
| <b>Item number</b> | R9114000   |

## Installation in different wall types

|   |   |   |
|---|---|---|
|    | <b>Concrete &gt;B25</b><br>V8605 - Mounting kit, 4 coach screws Ø10 x 70, plugs SX12, with grey screw covers.<br>To be ordered separately.  |    |
|   | <b>Solid Brick &gt;= Mz12</b><br>V8605 - Mounting kit, 4 coach screws Ø10 x 70, plugs SX12, with grey screw covers.<br>To be ordered separately.  |   |
|  | <b>Solid Sand Lime Brick &gt;= Hlz12</b><br>V8605 - Mounting kit, 4 coach screws Ø10 x 70, plugs SX12, with grey screw covers.<br>To be ordered separately.   |  |
|  | <b>Aerated Concrete P4</b><br>V8655 - Mounting kit, 4 coach screws Ø10 x 70, plugs GB14, with grey screw covers.<br>To be ordered separately.   |  |
|  | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b><br>V8605 - Mounting kit, 4 coach screws Ø10 x 70, plugs SX12, with white screw covers. NB! Plugs are not needed.<br>To be ordered separately. |  |



# PRESSALIT®

|   |  |   |   |
|---|--|---|---|
| <b>Product</b><br><b>Item number</b>  | SELECT TL4 toilet lifter, electrical, for floor outlet<br>R9114000   |   |   |
|    | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b><br>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.       |    |   |
|    | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</b><br>Wall fasteners (4 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar. |    |   |
|  | <b>Drywall (2 x 12,5 mm) water-resistant</b><br>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.   |  |   |

[pressalit.com](http://pressalit.com)