




# PRESSALIT®

|                                                  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
|--------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b><br><b>Item number</b>             | INDIVO lift for worktop 2401-3000 mm<br>RK1414000                                                                                                                                                                                                                                                                                                                                                                                                                        |
| <b>Colour</b>                                    | <p>EAN:5708590378848</p> <p>White</p>                                                                                                                                                                                                                                                                                                                                                 |
| <b>Product description</b>                       | <p>The name INDIVO relates to the individual configuration of the products. Lifts are available for worktops of any length between 600 mm and 3000 mm.</p> <p>INDIVO lift for worktop, with two motors and control box.<br/> Incl. cross brace and five brackets.<br/> Height adjustable up to 300 mm with switch or wired remote control.<br/> For worktop length 2401-3000 mm. Please indicate length and depth of worktop when ordering.<br/> Excl. mounting kit.</p> |
| <b>Adjustability</b><br><b>Adjustment height</b> | <p>Height adjustable</p> <p>300 mm</p>                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| <b>Product capacity</b>                          | <p>Maximum load: 100 kg, this includes the weight of the worktop.<br/> The load must be evenly distributed.</p>                                                                                                                                                                                                                                                                                                                                                          |
| <b>Speed upwards</b>                             | <p>Speed up mm: 20 mm/s<br/> Speed down mm: 20 mm/s</p>                                                                                                                                                                                                                                                                                                                                                                                                                  |
| <b>Noise level</b>                               | <p>45 dB</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| <b>Materials</b>                                 | <p>Lifting columns: Powder-coated steel<br/> Cross brace: Aluminium<br/> Brackets: Powder-coated steel</p>                                                                                                                                                                                                                                                                                                                                                               |
| <b>Ergonomy</b>                                  | <p>An electric height-adjustable kitchen worktop is ideal in all situations where various users - both seated and standing - use the same kitchen.<br/> This is equally true in private homes as well as larger centres with common kitchen facilities such as group homes and care centres.</p>                                                                                                                                                                         |
| <b>Features</b>                                  | <p>Lifts are height adjusted either via switches in the front edge or with a wired remote control.</p>                                                                                                                                                                                                                                                                                                                                                                   |



# PRESSALIT®

|                                         |                                                                                                                                |
|-----------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b>                          | INDIVO lift for worktop 2401-3000 mm                                                                                           |
| <b>Item number</b>                      | RK1414000                                                                                                                      |
| <b>Actuator (motor)</b>                 | DL17 Deskline (Linak) 70N, IP22                                                                                                |
| <b>Control box</b>                      | CBD6S (Linak) IP22                                                                                                             |
| <b>Wired remote control</b>             | HB53 (Linak), IPX1                                                                                                             |
| <b>Power consumption (maximum load)</b> | Power consumption by maximum load, watt: 300 W<br>Power consumption by standby: 2 W                                            |
| <b>Warranty</b>                         | Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date. |












|                                  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
|----------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product</b>                   | INDIVO lift for worktop 2401-3000 mm                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| <b>Item number</b>               | RK1414000                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| <b>Cleaning</b>                  | <p>INDIVO lift for kitchen worktop.<br/>The product is to be cleaned with hot water or a mild soapy cleaning agent.<br/>Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p><b>DISINFECTANTS:</b><br/>Clinimax Difficil-S<br/>Erisan OXY+<br/>Sprit (husholdningssprit)<br/>Suma Bac D10<br/>Virkon<br/>Rodalon Desinfektionsspray<br/>Lysoformin Spezial<br/>CaviCide<br/>Sufanios Premium<br/>Tvättsprit 70%</p> <p><b>NON-DISINFECTANTS:</b><br/>Suma Star free D1<br/>Taski 100<br/>Taski 200<br/>Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p><b>DECALCIFICATION OF ALUMINUM PARTS:</b><br/>Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts must be wiped over with a damp cloth wrung out in clear water.</p> |
| <b>Declaration of conformity</b> | <p>CE UK RoHS_LVD_EMC This product is in compliance with relevant requirements in:</p> <ul style="list-style-type: none"><li>- the RoHS Directive 2011/65/EU</li><li>- the EMC Directive 2014/30/EU</li><li>- the Low Voltage Directive 2014/35/EU.</li></ul> <p>Furthermore, for the UK, in compliance with relevant requirements in:</p> <ul style="list-style-type: none"><li>- The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012</li><li>- The Electromagnetic Compatibility Regulations 2016</li><li>- The Electrical Equipment (Safety) Regulations 2016</li></ul>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |









|                    |                                      |
|--------------------|--------------------------------------|
| <b>Product</b>     | INDIVO lift for worktop 2401-3000 mm |
| <b>Item number</b> | RK1414000                            |

## Installation in different wall types

|                                                                                     |                                                                                                                                                                                                       |                                                                                       |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|    | <p><b>Concrete &gt;B25</b></p> <p>V8608 - Mounting kit, 6 coach screws Ø10 x 70 - plugs SX12.<br/>To be ordered separately.</p>                                                                       |    |
|   | <p><b>Solid Brick &gt;= Mz12</b></p> <p>V8608 - Mounting kit, 6 coach screws Ø10 x 70 - plugs SX12.<br/>To be ordered separately.</p>                                                                 |   |
|  | <p><b>Solid Sand Lime Brick &gt;= Hlz12</b></p> <p>V8608 - Mounting kit, 6 coach screws Ø10 x 70 - plugs SX12.<br/>To be ordered separately.</p>                                                      |  |
|  | <p><b>Aerated Concrete P4</b></p> <p>V8658 - Mounting kit, 6 coach screws Ø10 x 70 - plugs GB14.<br/>To be ordered separately.</p>                                                                    |  |
|  | <p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b></p> <p>V8608 - Mounting kit, 6 coach screws Ø10 x 70 - plugs SX12. NB! Plugs are not needed.<br/>To be ordered separately.</p> |  |



# PRESSALIT®

| Product<br>Item number                                                              | INDIVO lift for worktop 2401-3000 mm<br>RK1414000                                                                                                                                                              |                                                                                       |                                                                                       |
|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|    | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b><br>Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.       |    |    |
|    | <b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</b><br>Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar. |    |    |
|  | <b>Drywall (2 x 12,5 mm) water-resistant</b><br>Wall fasteners (6 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.                                       |  |  |

It is the responsibility of the installer to ensure that suitable wall fasteners are used.

[pressalit.com](http://pressalit.com)

Pressalit A/S  
 Pressalitvej 1  
 DK-8680 Ry  
 Tel.: +45 8788 8788  
 Fax: +45 8788 8789  
 E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®