




Product Item number	INDIVO lift for countertop 78.8" - 94.5" RK1853202
Color Product description	EAN:5708590379111  <p>Gray (RAL 9006)</p> <p>The name INDIVO relates to the individual configuration of the products. Lifts are available for countertops of any length between 23.6" and 11.8".</p> <p>INDIVO lift for countertop, with three motors and control box. Max. load: 330 lbs including the countertop. Incl. cross brace and four brackets. Height adjustable up to 11.8" with switch or wired remote control. For countertop length 78.8" - 94.5". Please indicate length and depth of countertop when ordering. Excl. mounting kit.</p>
Adjustability Adjustment height Product capacity Speed up Noise level	Height adjustable 11,82 inch Maximum load: 330 lbs, this includes the weight of the countertop. The load must be evenly distributed. Speed up: 0,79 inch/s Speed down: 0,79 inch/s 45 dB
Materials Ergonomy	Lifting columns: Powder-coated steel Cross brace: Aluminium Brackets: Powder-coated steel An electric height-adjustable kitchen countertop is ideal in all situations where various users - both seated and standing - use the same kitchen. This is equally true in private homes as well as larger centers with common kitchen facilities such as group homes and care centers.













Product	INDIVO lift for countertop 78.8" - 94.5"
Item number	RK1853202
Features	Lifts are height adjusted either via switches in the front edge or with a wired remote control.
Actuator (motor)	DL17 Deskline (Linak) 70N, IP22
Control box	CBD6S (Linak) IP22
Wired remote control	HB53 (Linak), IPX1
Power consumption (maximum load)	Power consumption by maximum load: 300 W Power consumption by standby: 2 W
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.
Cleaning	<p>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: CaviCide</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p>DECALCIFICATION OF ALUMINUM PARTS: Pressalit recommends that water deposits (Calcium, lime etc.) be removed from wall tracks and other aluminum parts using a solution of three parts of 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts should be wiped over with a damp cloth wrung out in plain water.</p>
Declaration of conformity	This product is solely intended for the US and Canada, and has no EU declaration of conformity.









Product	INDIVO lift for countertop 78.8" - 94.5"
Item number	RK1853202

Mounting in different wall types

	Concrete >B25 V8607 - Mounting kit, 9 lag bolts Ø 0.4" x 2.8" (Ø10 x 70 mm), plugs SX12. To be ordered separately.	
	Solid Brick >= Mz12 V8607 - Mounting kit, 9 lag bolts Ø 0.4" x 2.8" (Ø10 x 70 mm), plugs SX12. To be ordered separately.	
	Solid Sand Lime Brick >= Hlz12 V8607 - Mounting kit, 9 lag bolts Ø 0.4" x 2.8" (Ø10 x 70 mm), plugs SX12. To be ordered separately.	
	Aerated Concrete P4 V8657 - Mounting kit, 9 lag bolts M0.4" x 2.8" (Ø10 x 70 mm), plugs GB14. To be ordered separately.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood V8607 - Mounting kit, 9 lag bolts Ø 0.4" x 2.8" (Ø10 x 70 mm), plugs SX12. NB! Plugs are not needed. To be ordered separately.	



Product Item number	INDIVO lift for countertop 78.8" - 94.5" RK1853202	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood Wall fasteners (9 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or Wingt anchors or similar.	
	Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (.08 inch) Wall fasteners (9 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or Wingt anchors or similar.	
	Drywall (2 x 12,5 mm) water-resistant Wall fasteners (9 pcs) must be bought separately, for drywall it is possible to use e.g. SnapTight or Wingt anchors or similar.	

It is the responsibility of the installer to ensure that suitable wall fasteners are used.