



<p><b>Product</b></p> <p><b>Item number</b></p>	<p>INDIVO lift for wall cabinets 15.7"-47.2"</p> <p>RK1820</p>
<p><b>Product description</b></p>	<p>EAN:5708590379067</p> <div data-bbox="1018 481 1391 846" data-label="Image"> </div> <p>The name INDIVO relates to the individual configuration of the products.</p> <p>INDIVO lift for wall cupboards, with one motor and control box. Max. load: 240 lbs including the cabinet.</p> <p>Height adjustable 16.9" with switches or wired remote control. When height adjusting downward, the lift will also move 7.1" towards the user.</p> <p>For wall cabinets width 15.7"-47.2". Please indicate height, width and depth of wall cabinets when ordering.</p> <p>Excl. mounting kit.</p>
<p><b>Adjustability</b></p> <p><b>Adjustment height</b></p> <p><b>Product capacity</b></p> <p><b>Speed up</b></p> <p><b>Noise level</b></p>	<p>Height adjustable</p> <p>16,94 inch</p> <p>Max. load (including cabinets): 1 lift: 240 lbs.</p> <p>Speed up: 0,71 inch/s Speed down: 0,71 inch/s</p> <p>45 dB</p>
<p><b>Materials</b></p> <p><b>Ergonomy</b></p>	<p>Material: Lift motor: Steel Cross braces: Aluminium Switches: ABS plastic</p> <p>Wall cabinets are moved diagonally, that is both vertically and towards the user. This makes it easy for seated users and children to see and access covered contents.</p> <p>Height-adjustable wall cabinets provide extra storage options in kitchens where cabinets cannot be installed under countertops out of consideration for seated users.</p>



<b>Product</b>	INDIVO lift for wall cabinets 15.7"-47.2"
<b>Item number</b>	RK1820
<b>Features</b>	<p>Lift heights for wall cabinets are adjusted via switches in the front countertop edge. Operating switches can be placed wherever you want along the front edge. The switches are color-coded - aluminium to operate countertops, and red to operate wall cabinets.</p> <p>The design of the lifts ensures that the lift motors are as discreet as possible, regardless of the cabinet position.</p> <p>When the wall cabinets are lowered 41.2" to their lowest position, they are also extended 7" towards the user.</p>
<b>Actuator (motor)</b>	DB4 Deskline (Linak) 1000 N, IP22
<b>Control box</b>	CBD6 (Linak)
<b>Wired remote control</b>	HB53 (Linak), IPX1
<b>Warranty</b>	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.
<b>Cleaning</b>	<p>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p><b>DISINFECTANTS:</b> CaviCide</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p><b>DECALCIFICATION OF ALUMINUM PARTS:</b> Pressalit recommends that water deposits (Calcium, lime etc.) be removed from wall tracks and other aluminum parts using a solution of three parts of 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts should be wiped over with a damp cloth wrung out in plain water.</p>
<b>Declaration of conformity</b>	This product is solely intended for the US and Canada, and has no EU declaration of conformity.



PRESSALIT®

---

<b>Product</b>	INDIVO lift for wall cabinets 15.7"-47.2"
<b>Item number</b>	RK1820

---

---

[pressalit.com](http://pressalit.com)

---

Pressalit A/S  
Pressalitvej 1  
DK-8680 Ry  
Tel.: +45 8788 8788  
Fax: +45 8788 8789  
E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

PRESSALIT®