




Product Item number	INDIVO lift for wall cabinets 15.7"-47.2" RK1820
Product description	EAN:5708590379067  <p>The name INDIVO relates to the individual configuration of the products.</p> <p>INDIVO lift for wall cupboards, with one motor and control box. Max. load: 240 lbs including the cabinet. Height adjustable 16.9" with switches or wired remote control. When height adjusting downward, the lift will also move 7.1" towards the user. For wall cabinets width 15.7"-47.2". Please indicate height, width and depth of wall cabinets when ordering. Excl. mounting kit.</p>
Adjustability Adjustment height Product capacity Speed up Noise level	Height adjustable 16,94 inch Max. load (including cabinets): 1 lift: 240 lbs. Speed up: 0,71 inch/s Speed down: 0,71 inch/s 45 dB
Materials Ergonomy	Material: Lift motor: Steel Cross braces: Aluminium Switches: ABS plastic Wall cabinets are moved diagonally, that is both vertically and towards the user. This makes it easy for seated users and children to see and access covered contents. Height-adjustable wall cabinets provide extra storage options in kitchens where cabinets cannot be installed under countertops out of consideration for seated users.



Product	INDIVO lift for wall cabinets 15.7"-47.2"
Item number	RK1820
Features	<p>Lift heights for wall cabinets are adjusted via switches in the front countertop edge. Operating switches can be placed wherever you want along the front edge. The switches are color-coded - aluminium to operate countertops, and red to operate wall cabinets.</p> <p>The design of the lifts ensures that the lift motors are as discreet as possible, regardless of the cabinet position.</p> <p>When the wall cabinets are lowered 41.2" to their lowest position, they are also extended 7" towards the user.</p>
Actuator (motor)	DB4 Deskline (Linak) 1000 N, IP22
Control box	CBD6 (Linak)
Wired remote control	HB53 (Linak), IPX1
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.



Product	INDIVO lift for wall cabinets 15.7"-47.2"
Item number	RK1820
Cleaning	<p>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningsprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p>DECALCIFICATION OF ALUMINUM PARTS: Pressalit recommends that water deposits (Calcium, lime etc.) be removed from wall tracks and other aluminum parts using a solution of three parts of 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts should be wiped over with a damp cloth wrung out in plain water.</p>
Declaration of conformity	<p>This product is solely intended for the US and Canada, and has no EU declaration of conformity.</p>



PRESSALIT®

Product	INDIVO lift for wall cabinets 15.7"-47.2"
Item number	RK1820

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®