




PRESSALIT®

Product Item number	INDIVO lift for wall cabinets 47.3"-94.5" RK1821
Product description	<p>EAN:5708590379074</p>  <p>The name INDIVO relates to the individual configuration of the products.</p> <p>INDIVO lift for wall cupboards, with two motors and control box. Max. load: 485 lbs including the cabinets.</p> <p>Height adjustable 16.9" with switches or wired remote control. When height adjusting downward, the lift will also move 7.1" towards the user.</p> <p>For wall cabinets width 47.3"-94.5". Please indicate height, width and depth of wall cabinets when ordering.</p> <p>Excl. mounting kit.</p>
Adjustability Adjustment height Product capacity Speed up Noise level	<p>Height adjustable</p> <p>16,94 inch</p> <p>Max. load (including cabinets): 2 lifts: 485 lbs.</p> <p>Speed up: 0,71 inch/s Speed down: 0,71 inch/s</p> <p>45 dB</p>
Materials Ergonomy	<p>Material: Lift motor: Steel Cross braces: Aluminium Switches: ABS plastic</p> <p>Wall cabinets are moved diagonally, that is both vertically and towards the user. This makes it easy for seated users and children to see and access covered contents.</p> <p>Height-adjustable wall cabinets provide extra storage options in kitchens where cabinets cannot be installed under countertops out of consideration for seated users.</p>



Product	INDIVO lift for wall cabinets 47.3"-94.5"
Item number	RK1821
Features	<p>Lift heights for wall cabinets are adjusted via switches in the front countertop edge. Operating switches can be placed wherever you want along the front edge. The switches are color-coded - aluminium to operate countertops, and red to operate wall cabinets.</p> <p>The design of the lifts ensures that the lift motors are as discreet as possible, regardless of the cabinet position.</p> <p>When the wall cabinets are lowered 41.2" to their lowest position, they are also extended 7" towards the user.</p>
Actuator (motor)	DB4 Deskline (Linak) 1000 N, IP22
Control box	CBD6 (Linak)
Wired remote control	HB53 (Linak), IPX1
Warranty	Pressalit makes a commitment to remedy material and manufacturing defects for a period of three years from the invoicing date.



PRESSALIT®

Product	INDIVO lift for wall cabinets 47.3"-94.5"
Item number	RK1821
Cleaning	<p>This product should be cleaned with hot water or a mild cleaning solution. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p>DISINFECTANTS: Clinimax Difficil-S Erisan OXY+ Sprit (husholdningssprit) Suma Bac D10 Virkon Rodalon Desinfektionsspray Lysoformin Spezial CaviCide Sufanios Premium Tvättsprit 70%</p> <p>NON-DISINFECTANTS: Suma Star free D1 Taski 100 Taski 200 Milizid Citro</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p>DECALCIFICATION OF ALUMINUM PARTS: Pressalit recommends that water deposits (Calcium, lime etc.) be removed from wall tracks and other aluminum parts using a solution of three parts of 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts should be wiped over with a damp cloth wrung out in plain water.</p> <p>This product is solely intended for the US and Canada, and has no EU declaration of conformity.</p>
Declaration of conformity	



PRESSALIT®

Product	INDIVO lift for wall cabinets 47.3"-94.5"
Item number	RK1821

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®